

## Ceiling TV Mount - 8.2' to 9.8' Long Pole

Product ID: FPCEILPTBLP



This ceiling TV mount supports VESA mount compatible TVs from 32" to 75" in size, with a weight capacity of up to 110 lb. (50 kg). It lets you save wall and floor space by hanging your flat-panel LCD, LED or plasma TV from the ceiling in a prominent area.

The ceiling mount is ideal for use in lobbies, entrances or other areas with high ceilings.

### Adjustable Height


With a telescopic pole, the TV mount lets you suspend a display at your desired distance from the ceiling. This works well with a range of ceiling heights. The steel pole can extend from 8.2 to 9.84 ft. (2.5 to 3 m), with a total lift (height extension) of 19.6" (.5 m).

## Swivels to Suit Your Ceiling

The flat-screen ceiling mount accommodates a wide variety of ceiling types. You can swivel the TV to work with virtually any type of ceiling for level viewing, including sloped ceilings (up to 60 degrees), and pitched or horizontal (flat) ceilings.

## Viewable from Any Direction

You can adjust your TV to create a comfortable viewing angle, by tilting it up to -25 degrees down towards your audience for optimum visibility. Plus, the full-motion mount lets you swivel your display around the pole + 180 / - 180 degrees, without using tools.



## Hook-and-Mount Design

Simply attach the included vertical brackets, with built-in hooks, to the back of your TV. Once attached, hang your TV securely onto the ceiling mount. The preset leveling adjustments ensure ideal positioning after hanging.

FPCEILPTBLP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Suspend a flat-screen TV in an area with a high ceiling
- Ideal for lobbies and entrance ways
- Keep your guests informed and entertained

### Features

- Save space by suspending your 32" to 75" flat-screen TV from the ceiling
- Long pole with min-max length extension of 8.2 to 9.8' (2.5 to 3 m) for versatile use
- Ceiling TV mount swivels +60 /-60 degrees to adjust to sloped or level ceilings
- Full-motion mount lets you swivel the display +180 /-180 degrees around the pole and tilt downwards -25 degrees, without using tools
- Durable steel mount supports TVs up to 110 lb.(50 kg)
- Easy setup, with a hook-and-mount design

<b>Hardware</b>	Warranty	3 Years
	# of Displays Supported	2
	Cable Management	Yes
	Mounting Options	Ceiling Mount
	VESA Hole Pattern(s)	200x200 mm
		300x300 mm
		400x200 mm
400x400 mm		
600x400 mm		
Wallmountable	No	
<b>Performance</b>	Anti-theft	No
	Height Adjustment	Yes
	Maximum Display Size	75"
	Maximum Height	9.8 ft [3 m]
	Minimum Display Size	32"
	Minimum Height	8.2 ft [2.5 m]
	Swivel / Pivot	+180° to -180°
	Tilt	+0° / -25°
	Video Wall	No
	Weight Capacity (Per Display)	110.5 lb [50 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Product Height	126.7 in [3218 mm]
	Product Length	26.8 in [680 mm]
	Product Weight	22.1 lb [10 kg]
	Product Width	17.1 in [435 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	24 lb [10.8 kg]
<b>What's in the Box</b>	Included in Package	1 - ceiling mount and pole
		1 - middle pole
		1 - lower pole

- 1 - TV mount
- 2 - vertical brackets
- 1 - horizontal bracket
- 2 - M8x55 mm screws
- 2 - M8x60 mm screws
- 4 - nuts
- 1 - wrench
- 1 - hex key
- 1 - mounting template
- 4 - M5x14 mm screws
- 4 - M6x14 mm screws
- 4 - M6x30 mm screws
- 4 - M8x30 mm screws
- 4 - M8x50 mm screws
- 4 - rectangular washers
- 8 - small spacers
- 8 - large spacers
- 4 - screws
- 4 - concrete anchors
- 4 - circular washers
- 1 - instruction manual

---

Product appearance and specifications are subject to change without notice.