

## Low-Profile TV Wall Mount - Tilting

Product ID: FPWTLTBAT



Save space while improving the appearance of your work area, with this low-profile TV wall mount. The mount sits close to the wall to support a VESA Mount compliant TV from 37" to 75", and offers anti-theft protection as well as tilting capability that makes it easy to find the perfect viewing position.

### Low-Profile Design for Meeting Areas or Digital Signage

Mount your flat-screen TV or monitor in a location that's convenient for visitors, clients or employees. The wall mount safely and securely supports your TV about two inches (51 mm) from the wall to provide a sleek, low-profile look.

It's ideal for lobbies, hallways, boardrooms, works areas, customer-facing areas or for creating digital signage. The wall mount supports most 37" to 75" (940 to 1905 mm) LED or LCD flat panel TVs weighing up to 88 lb. (40 kg).

## Adjust Your Viewing Angle

This TV wall mount tilts -10 to +5 degrees, so you can adjust the angle of your display with ease to customize your viewing experience.

## Anti-theft Protection

Engineered with heavy-duty steel, the robust steel TV wall mount securely supports your flat-screen TV, to protect your investment. Ideal for areas with high traffic and minimal supervision, the TV mount features a steel bar that can be locked into place with a padlock (purchased separately) to protect your TV or monitor against theft.

## Easy Setup

A built-in level helps to ensure your TV is aligned in a straight position on your wall, to ensure optimum viewing.

The FPWTLTBAT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Securely wall-mount a TV
- Keep guests informed and entertained
- Ideal for classrooms, lecture halls or customer-facing areas
- Protect your TV or monitor against theft

### Features

- Save space with this flat-screen TV wall mount for 37" to 75" TVs (fits curved TVs, with compatible VESA mount)
- Low profile TV mount sits only 2" (51 mm) from the wall
- Tilts -10 to +5 degrees for optimal viewing
- Lockable bar securely holds TV and provides anti-theft protection (padlock required)
- Heavy-duty steel TV wall mount (tool-less assembly) supports up to 88 lb. (40 kg)

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	1
	Articulating	No
	Cable Management	No
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	200x200 mm
		300x300 mm
		400x200 mm
400x400 mm		
600x400 mm		
800x400 mm		
<b>Performance</b>	Anti-theft	Yes
	Fits Curved TV	Yes
	Maximum Display Size	75"
	Minimum Display Size	37"
	Video Wall	No
	Weight Capacity (Per Display)	88.4 lb [40 kg]
<b>Physical Characteristics</b>	Product Height	17.3 in [440 mm]
	Product Length	39.3 in [998 mm]
	Product Weight	8.1 lb [3.7 kg]
	Product Width	2 in [51 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	10.5 lb [4.8 kg]
<b>What's in the Box</b>	Included in Package	1 - wall mount
		1 - safety bar
		1 - left adapter bracket
		1 - right adapter bracket
		1 - level
		2 - decorative covers
		4 - decorative cover screws
		4 - M5x14 mm screws

- 4 - M6x14 mm screws
- 4 - M8x50 mm screws
- 4 - M6x30 mm screws
- 4 - M8x30 mm screws
- 4 - rectangular washers
- 8 - small spacers
- 8 - large spacers
- 6 - screws
- 6 - concrete anchors
- 6 - circular washers
- 1 - instruction manual

---

Product appearance and specifications are subject to change without notice.