

# HDMI to VGA Converter with Audio - Compact - 1920x1200

Product ID: HD2VGAMICRA



This HDMI® to VGA adapter lets you connect your HDMI computer to a VGA display or projector. The versatile adapter features a discrete 3.5mm audio output for extracting stereo audio from your HDMI signal, and supports PC resolutions up to 1920x1200.

## Versatile VGA compatibility

The adapter works with any HDMI equipped computer to add compatibility with VGA displays. Enabling VGA support on your Ultrabook™ or Chromebook™ means that you'll have the connection options you need to use almost any boardroom projector or display.

## Effortless setup and operation

The HDMI to VGA adapter doesn't require software or drivers, which saves you time and hassle when you need to make a quick connection. Plus, the adapter features a 3.5mm output which gives you the option to share the audio directly from your HDMI port.

### **Compact for maximum portability**

This compact HDMI to VGA adapter is lightweight and portable, and easily fits into any laptop carrying bag. The adapter has also been engineered with low-power architecture, so you won't need to carry a bulky external power adapter, or find access to an electrical outlet while you're on the go.

This converter will not output digitally encrypted content.

The HD2VGAMICRA is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect your Ultrabook or Chromebook to a boardroom display
- Use your VGA monitor as secondary display
- Carry the adapter with you while travelling to ensure your laptop is compatible with VGA displays in BYOD applications

### Features

- Increase the compatibility of your HDMI equipped Ultrabook or Chromebook by adding support for VGA
- Hassle-free setup, through plug-and-play installation
- Maximum portability with a small foot print and lightweight design
- Supports resolutions up to 1920x1200 (1080p)
- Discrete 3.5mm audio output

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	Audio	Yes
	AV Input	HDMI
	AV Output	VGA
	Chipset ID	Chrontel - CH7101A-BF
	Ports	1
<b>Performance</b>	Audio Specifications	2-channel stereo (3.5mm)
	Maximum Digital Resolutions	1900x1200 @ 60Hz
	Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720  Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - HDMI (19 pin) Male Input
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female Output  1 - 3.5 mm Mini-Jack (3 Position) Female Output
	<b>Special Notes / Requirements</b>	<b>Note</b>  This converter is not compatible with Mac computers that use Intel HD 4000 cards (Mac Mini), for specific support for these devices StarTech.com offers the Mac Mini to VGA adapter - <a href="#">MCHD2VGA</a> .  This converter will not output digitally encrypted content.
<b>Environmental</b>	Humidity	90% RH
	Operating Temperature	10°C to 40°C (50°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
<b>Physical Characteristics</b>	Color	Black
	Product Height	0.5 in [12.5 mm]
	Product Length	2.5 in [62.3 mm]
	Product Weight	0.3 oz [8 g]
	Product Width	0.8 in [21 mm]

<b>Packaging Information</b>	Shipping (Package) Weight	1.3 oz [38 g]
<b>What's in the Box</b>	Included in Package	1 - Compact HDMI to VGA adapter

Product appearance and specifications are subject to change without notice.