

HDMI to VGA Converter with Audio - Compact - 1920x1200

Product ID: HD2VGAMICRA



This HDMI® to VGA adapter lets you connect your HDMI computer to a VGA display or projector. The versatile adapter features a discrete 3.5mm audio output for extracting stereo audio from your HDMI signal, and supports PC resolutions up to 1920x1200.

Versatile VGA compatibility

The adapter works with any HDMI equipped computer to add compatibility with VGA displays. Enabling VGA support on your Ultrabook™ or Chromebook™ means that you'll have the connection options you need to use almost any boardroom projector or display.

Effortless setup and operation

The HDMI to VGA adapter doesn't require software or drivers, which saves you time and hassle when you need to make a quick connection. Plus, the adapter features a 3.5mm output which gives you the option to share the audio directly from your HDMI port.

Compact for maximum portability

This compact HDMI to VGA adapter is lightweight and portable, and easily fits into any laptop carrying bag. The adapter has also been engineered with low-power architecture, so you won't need to carry a bulky external power adapter, or find access to an electrical outlet while you're on the go.

This converter will not output digitally encrypted content.

The HD2VGAMICRA is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your Ultrabook or Chromebook to a boardroom display
- Use your VGA monitor as secondary display
- Carry the adapter with you while travelling to ensure your laptop is compatible with VGA displays in BYOD applications

Features

- Increase the compatibility of your HDMI equipped Ultrabook or Chromebook by adding support for VGA
- Hassle-free setup, through plug-and-play installation
- Maximum portability with a small foot print and lightweight design
- Supports resolutions up to 1920x1200 (1080p)
- Discrete 3.5mm audio output

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	Audio	Yes
	AV Input	HDMI
	AV Output	VGA
	Chipset ID	Chrontel - CH7101A-BF
	Ports	1
Performance	Audio Specifications	2-channel stereo (3.5mm)
	Maximum Digital Resolutions	1900x1200 @ 60Hz
	Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - HDMI (19 pin) Male Input
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female Output 1 - 3.5 mm Mini-Jack (3 Position) Female Output
	Special Notes / Requirements	Note This converter is not compatible with Mac computers that use Intel HD 4000 cards (Mac Mini), for specific support for these devices StarTech.com offers the Mac Mini to VGA adapter - MCHD2VGA . This converter will not output digitally encrypted content.
Environmental	Humidity	90% RH
	Operating Temperature	10°C to 40°C (50°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Physical Characteristics	Color	Black
	Product Height	0.5 in [12.5 mm]
	Product Length	2.5 in [62.3 mm]
	Product Weight	0.3 oz [8 g]
	Product Width	0.8 in [21 mm]

Packaging Information	Shipping (Package) Weight	1.3 oz [38 g]
What's in the Box	Included in Package	1 - Compact HDMI to VGA adapter

Product appearance and specifications are subject to change without notice.