

HDMI to Composite Converter with Audio

Product ID: HD2VID



The HD2VID HDMI® to Composite Video Converter (with Audio) converts a digital HDMI video source (with supporting audio) to work with analog Composite video televisions and displays in both NTSC and PAL systems.

The HDMI to Composite converter provides features that ensure the highest quality output image, such as noise reduction, frame rate conversion and adaptive contrast enhancement, while an easy to use On-Screen Display(OSD) allows you to monitor your display status. Support for a wide range of HDTV and PC input resolutions make this versatile HDMI converter a perfect solution for using newer devices with existing legacy displays.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for converting newer HDMI devices to work with older composite or S-Video televisions
- Great for use in presentations, tradeshows, conferences, retail, entertainment, and home video applications

Features

- Converts HDMI® source to NTSC or PAL
- Converts HDMI audio to analog stereo RCA Audio
- Supports input HDTV resolutions up to 720p (PC up to 1280x800)
- Output picture size Underscan / Overscan
- Adaptive contrast enhancement
- Supports output resolutions of 480i/576p

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	HDMI
	AV Output	Audio RCA Composite
	Industry Standards	Standard HDMI, DVI 1.0
Performance	Audio Specifications	Input - LPCM 2Ch, 48kHz Output - Stereo L/R
	Supported Resolutions	Input TV - 720p, 576p, 480p @ 60Hz PC - 1280x800, 1280x768, 1224x768, 800x600, 640x480 @ 60Hz Output 480i, 576p
Connector(s)	Connector A	1 - HDMI (19 pin) Female Input
	Connector B	1 - Composite Video (1 x RCA) Female Output 1 - Stereo Audio (2 x RCA) Female Output
Power	Center Tip Polarity	Positive
	Input Current	0.3 A
	Input Voltage	110V-240V AC
	Output Current	1A
	Output Voltage	5 DC
	Plug Type	M
	Power Consumption (In Watts)	3
	Power Source	AC Adapter Included
Environmental	Humidity	20~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	White
	Enclosure Type	Plastic
	Product Height	1 in [26 mm]
	Product Length	3.9 in [100 mm]

	Product Weight	2.9 oz [81 g]
	Product Width	2.5 in [64 mm]
Packaging Information	Shipping (Package) Weight	11.3 oz [321 g]
What's in the Box	Included in Package	1 - HDMI® to Composite Converter 1 - Universal Power Adapter (NA/UK/EU/AU) 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.