

HDMI or DVI to DisplayPort Active Converter

Product ID: HDMI2DP



The HDMI2DP DVI or HDMI® to DisplayPort® Converter converts an HDMI, DVI or Mini DVI input signal into a DisplayPort (or Mini DisplayPort) output, eliminating the cost of upgrading your source device hardware or purchasing a new display.

With support for full HD resolutions up to 1920x1200, the HDMI2DP converter is the perfect solution for connecting devices that have an HDMI, DVI single-link or mini DVI output, such as video cards (desktop or laptop), video game consoles or home theater receivers, to your DisplayPort-capable display.

To connect a DVI video source to this adapter, a DVI to HDMI adapter is required. The following StarTech.com adapters are compatible with this adapter:

[3 ft HDMI to DVI-D Cable \(HDDVIMM3\)](#)

[6 ft HDMI to DVI-D Cable \(HDMIDVIMM6\)](#)

[8in HDMI to DVI-D Video Cable Adapter \(HDDVIMF8IN\)](#)

[HDMI to DVI-D Video Cable Adapter - M/F \(HDMIDVIMF\)](#)

[Mini DVI to HDMI Video Adapter for Macbooks and iMacs \(MDVIHDMIMF\)](#)

The HDMI2DP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing DisplayPort® monitor to be used with your HDMI® or DVI device

Features

- Supports full HD resolutions up to 1920x1200
- Stores EDID information to ensure compatibility between source and display
- Supports HDMI® uncompressed 2-channel audio such as LPCM
- Allows for conversion of DVI or mini-DVI sources with additional cables (not included)
- Compatible with HDMI®, DVI and Mini DVI 1.0 Input
- Supports DisplayPort®/Mini DisplayPort 1.1a output

| | | |
|---------------------------------|------------------------------|--|
| Hardware | Warranty | 2 Years |
| | Active or Passive Adapter | Active |
| | Audio | Yes |
| | AV Input | HDMI |
| | AV Output | DisplayPort |
| Performance | Audio Specifications | 5.1 Surround Sound |
| | Maximum Digital Resolutions | 1920x1200 (50/60Hz) |
| Connector(s) | Connector A | 1 - HDMI (19 pin) Female Input |
| | Connector B | 1 - DisplayPort (20 pin) Female Output |
| Indicators | LED Indicators | 1 - Red Power LED |
| Power | Center Tip Polarity | Positive |
| | Input Current | 0.5A |
| | Input Voltage | 100 ~ 240 AC |
| | Output Current | 2A |
| | Output Voltage | 5 DC |
| | Plug Type | N |
| | Power Consumption (In Watts) | 5 |
| | Power Source | AC Adapter Included |
| Environmental | Humidity | 5% to 90% RH (no condensation) |
| | Operating Temperature | 0°C to 70°C (32°F to 158°F) |
| | Storage Temperature | -10°C to 80°C (14°F to 176°F) |
| Physical Characteristics | Color | Black |
| | Enclosure Type | Steel |
| | Product Height | 0.9 in [23 mm] |
| | Product Length | 3.2 in [82 mm] |
| | Product Weight | 3.8 oz [109 g] |
| | Product Width | 1.7 in [43 mm] |
| Packaging Information | Shipping (Package) Weight | 13.8 oz [392 g] |
| What's in the Box | Included in Package | 1 - HDMI to DisplayPort converter |

1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand

1 - Instruction Manual

Product appearance and specifications are subject to change without notice.