

10m (33 ft) Active CL2 In-wall High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI - M/M

Product ID: HDMM10MA



The HDMM10MA 33 ft Active High Speed HDMI® Cable features a built-in active signal booster for a connection distance of up to 33 feet (10m) between your HDMI-enabled devices, with no signal loss.

This durable yet lightweight cable features thinner HDMI wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 10 meter HDMI cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., over long distances, with no signal loss

Features

- Built-in, active amplifier circuitry
- Supports Ultra HD Resolutions up to 4k x 2k
- Provides connection distances up to 33 feet away
- Gold-plated HDMI connectors
- High quality construction

| | | |
|---------------------------------|-----------------------------|----------------------------------------------------|
| Hardware | Warranty | 2 Years |
| | Cable Jacket Type | PVC - Polyvinyl Chloride |
| | Cable Shield Type | Aluminum-Mylar Foil with Braid |
| | Chipset ID | Redmere - PRE1692 |
| | Connector Plating | Gold |
| | Fire Rating | CL2 Rated |
| Performance | Maximum Digital Resolutions | 4K x 2K @ 30 Hz |
| Connector(s) | Connector A | 1 - HDMI (19 pin) Male |
| | Connector B | 1 - HDMI (19 pin) Male |
| Physical Characteristics | Cable Length | 32.8 ft [10 m] |
| | Cable OD | 0.3 in [7.5 mm] |
| | Color | Black |
| | Connector Style | Straight |
| | Product Length | 32.8 ft [10 m] |
| | Product Weight | 20.9 oz [593 g] |
| | Wire Gauge | 28 AWG |
| Packaging Information | Package Quantity | 1 |
| | Shipping (Package) Weight | 21.5 oz [610 g] |
| What's in the Box | Included in Package | 1 - 10m Active High Speed HDMI® Cable - HDMI - M/M |

Product appearance and specifications are subject to change without notice.