

High Speed HDMI Cable M/M - Active - CL2 In-Wall - 20 m (65 ft.)

Product ID: HDMM20MA



This active HDMI® cable offers a connection distance of up to 65 feet (20 meters) between your HDMI enabled devices. It meets CL2 rating safety requirements, so it's ideal for in-wall cable runs in your home and office installations.

Dependable connections over longer distances

The cable features built-in amplifier circuitry which actively boosts your HDMI signal, with no external power required. It's the perfect solution for longer transmissions without any signal loss.

Run in-wall cable installations

The HDMI cable is CL2 rated for in-wall installations, which makes them perfect for A/V installations in residential or office settings. You can set up your home theatre, gaming or audio-video equipment with the cables hidden away safely inside the walls and place your devices as needed throughout your work or living space.

Deliver astonishing 4k video

This high-quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM20MA is backed by StarTech.com's 2-year Warranty for guaranteed reliability.

Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the Source and Display labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility



Applications

- Connect your high-definition A/V devices such as streaming media players (Roku®, Apple TV), game consoles (Xbox One, PS4), Blu-ray Disc™ or DVD players over long distances, with no signal loss

Features

- Built-in, active amplifier circuitry for longer connections
- CL2-rated for in-wall installations
- Supports Ultra HD Resolutions up to 4k x 2k

Hardware	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Chipset ID	Redmere - RM1691
	Connector Plating	Gold
	Fire Rating	CL2 Rated
Performance	Maximum Digital Resolutions	4K x 2K @ 30 Hz
Connector(s)	Connector A	1 - HDMI (19 pin) Male
	Connector B	1 - HDMI (19 pin) Male
Physical Characteristics	Cable Length	65.6 ft [20 m]
	Cable OD	0.3 in [8.5 mm]
	Color	Black
	Connector Style	Straight
	Product Height	0.4 in [0.9 cm]
	Product Length	65.6 ft [20 m]
	Product Width	0.8 in [20 mm]
	Weight of Product	3 lb [1.4 kg]
	Wire Gauge	24 AWG
Packaging Information	Package Height	3.2 in [82 mm]
	Package Length	13.3 in [33.8 cm]
	Package Quantity	1
	Package Width	12.8 in [32.6 cm]
	Shipping (Package) Weight	3.8 lb [1.7 kg]
What's in the Box	Included in Package	1 - 20m Active CL2 In-Wall High Speed HDMI® Cable - HDMI - M/M

Product appearance and specifications are subject to change without notice.