

3 Bay Aluminum Trayless Hot Swap Mobile Rack Backplane for 3.5in SAS II/SATA III - 6 Gbps HDD

Product ID: HSB3SATSASBA



The HSB3SATSASBA Removable 3-drive backplane lets you quickly install and hot-swap 3.5" drives from the front of your computer, by turning two 5.25" bays into a hot-swappable interface for you to connect up to three 3.5" SATA or SAS hard drives (HDD).

For added versatility, the hard drive bay can interface with SATA I/II/III and SAS I/II hard drives -- an ideal accommodation for enterprise system applications.

For a quick and secure method of installing and removing drives, the backplane features ejection levers and a key-lock design. To help prevent drive failure, the bay provides excellent heat dissipation with a built-in fan, and a vented solid aluminum enclosure.

The HSB3SATSASBA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Imaging - for new system builds or configurations, use the hot swap bay in your master system to quickly copy the Windows OS to multiple blank hard drives
- Add a hot-swap bay to a server or workstation computer that you can use as a removable backup solution
- IT environments where you need to quickly insert/replace hard drives with no external HDD enclosure required

Features

- Solid aluminum construction
- Key lock design
- Built-in fan
- 3 drive bay design
- Installs in two 5.25" drive bays
- Trayless design for hot swap support
- Support for SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Support for SAS revision I/II (3.0/6.0 Gbps)
- UL VO flammability rating
- Power and Activity LEDs for each drive

Hardware	Warranty	2 Years	
	Compatible Drive Types	SAS & SATA	
	Drive Installation	Removable	
	Drive Size	3.5in	
	Fan Bearing Type	Sleeve Bearing	
	Fan(s)	Yes	
	Fans	1 - 70 mm	
	Front Door Key Lock	Yes	
	Interface	SATA	
	Number of Drives	3	
	Number of internal 3.5 inch bays	3	
Performance	Fan Specifications	Speed: 3000 RPM+10% Airflow: 27.60CFM (At zero static pressure) Noise level: 26.72dB-A	
	Max Drive Capacity	Currently tested with up to 4TB 7200 RPM hard drives	
	Maximum Data Transfer Rate	6 Gbit/s	
	Type and Rate	SATA III (6 Gbps)	
Connector(s)	Drive Connectors	3 - SFF-8482 (29 pin, Data & Power, Internal SAS) Receptacle	
	Host Connectors	2 - SATA Power (15 pin) Receptacle 3 - SATA (7 pin, Data) Receptacle	
Software	OS Compatibility	OS independent; No software or drivers required	
Indicators	LED Indicators	1 - Power LED 1 - Drive 1 Activity LED 1 - Drive 2 Activity LED 1 - Drive 3 Activity LED	
	Environmental	Humidity	5%~85% RH
	Operating Temperature	0°C to 55°C (23°F to 95°F)	
	Storage Temperature	-20°C to 60°C (-4°F to 122°F)	
Physical Characteristics	Color	Black	
	Enclosure Type	Aluminum	
	Product Height	4.3 in [11 cm]	

	Product Length	7.6 in [19.4 cm]
	Product Width	5.7 in [14.5 cm]
	Weight of Product	2.7 lb [1.2 kg]
Packaging Information	Package Height	4.8 in [12.3 cm]
	Package Length	10 in [25.3 cm]
	Package Width	7 in [17.9 cm]
	Shipping (Package) Weight	2.7 lb [1.2 kg]
What's in the Box	Included in Package	1 - 3 SATA HDD Backplane
		1 - Installation screw kit
		1 - Instruction Manual
		2 - Bay Key
		3 - 18" SATA Cable

Product appearance and specifications are subject to change without notice.