

3 ft 1s1p USB to Serial Parallel Port Adapter Cable

Product ID: ICUSB2321284



The ICUSB2321284 1S1P USB to Serial/Parallel Adapter Cable enables you to connect DB9 RS232 serial devices and IEEE 1284 parallel devices to your PC or Linux laptop or desktop computer, through a single USB port, as though the computer offered onboard connectors.

An innovative solution, the adapter cable features both a parallel and serial port that can be used simultaneously, delivering serial and parallel data rates of up to 921.6 Kbps and 1Mbps (respectively) to ensure optimum performance from your connected devices.

Simple to install and use, the serial/parallel USB adapter is a cost-effective solution that bridges the connectivity gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for IT Administrators looking to add legacy functionality to newer laptops, desktops and servers that lack integrated RS-232 Serial and/or Parallel ports
- Connect to console ports, UPS, and other devices in the server room/server closet
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync

Features

- Easy to setup and install - plug and play for most operating systems
- No external power needed - draws power from the USB connection
- Thin, lightweight design
- Supports serial baud rates of up to 921.6 Kbps
- Compatible with modems, printers, bar code scanners, servers, PDUs, and most other serial RS232 or Parallel equipment

Hardware	Warranty	3 Years
	Bus Type	USB 2.0
	Chipset ID	ASIX - MCS7715
	Industry Standards	RS232, IEEE 1284, USB 1.1
	Interface	Serial
	Port Style	Cable Adapters
	Ports	2
Performance	Data Bits	5, 6, 7, 8
	FIFO	192 Bytes
	Max Baud Rate	921.6 Kbps
	Parity	Even, Odd, Mark, Space, None
	Serial Protocol	RS-232
Connector(s)	Connector Type(s)	1 - DB-25 (25 pin, D-Sub) Female 1 - DB-9 (9 pin, D-Sub) Male 1 - USB Type-A (4 pin) USB 2.0 Male
	OS Compatibility	Windows® CE 5.0, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016 Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
	Humidity	0~65% RH
Environmental	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-20°C to 80°C (-4°F to 176°F)
	Cable Length	3 ft [0.9 m]
Physical Characteristics	Color	Black
	Enclosure Type	Plastic
	Product Length	39.4 in [1000 mm]
	Product Weight	2.4 oz [69 g]
	Shipping (Package) Weight	4 oz [114 g]
Packaging Information		
What's in the Box	Included in Package	1 - USB to Serial & Parallel cable 1 - Driver CD 1 - User Manual

Product appearance and specifications are subject to change without notice.