

2 Port Industrial USB to Serial RJ45 Adapter - Wallmount and DIN Rail

Product ID: ICUSB2322RJ



The ICUSB2322RJ 2-Port Industrial USB to Serial RJ45 Adapter (Wallmount and DIN Rail) allows you to add two RS232 serial connections using RJ45 signaling ports to a PC or Server through a single USB 2.0 port.

The RS232 to RJ45 adapter features COM port retention to maintain your port number assignments across a reboot and supports serial data rates up to 921 Kbps. The included DIN Rail clips (Top Hat) and wall-mounting brackets provide simple solutions for out of the way installations, while the sturdy metal enclosure offers durability in harsh industrial environments.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for IT Administrators looking to add legacy functionality to newer laptops, PCs and servers that lack integrated RS232
- Connect, monitor and control industrial/automotive sensors and equipment

Features

- Adds 2 RS232 serial RJ45 connectors via a single USB port
- Includes wallmount and Top-Hat DIN rail mounting brackets
- Supports data rates up to 921.6 Kbps
- COM Port retention
- USB-Powered - No external adapter required
- USB 2.0 High Speed (480Mbps) and Full Speed (12Mbps) supported
- USB connection features optional latching female screw holes for added security

Hardware	Warranty	2 Years
	Bus Type	USB 2.0
	Chipset ID	FTDI - FT232R
	Interface	Serial
	Port Style	External Hub
	Ports	2
Performance	Data Bits	7, 8
	FIFO	128 Bytes
	Max Baud Rate	921.6 Kbps
	Parity	Odd, Even, Mark, Space, None
	Serial Protocol	RS-232
	Stop Bits	1, 2
Connector(s)	Connector Type(s)	1 - USB B (4 pin) Female 2 - RJ-45 Female
Software	OS Compatibility	Windows® CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
Power	Power Source	USB-Powered
Environmental	Humidity	5~95% RH
	Operating Temperature	0°C to 55°C (32°F to 131°F)
	Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	0.8 in [20 mm]
	Product Length	2.6 in [65 mm]
	Product Weight	2.8 oz [78 g]
	Product Width	1.7 in [42 mm]
Packaging Information	Shipping (Package) Weight	0.6 lb [0.3 kg]
What's in the Box	Included in Package	1 - 2 Port USB to Serial RJ45 Adapter 1 - Wallmount Bracket

- 2 - DIN Rail Clips
- 1 - USB A to B Cable
- 1 - Driver CD
- 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.