

## 3m External Mini SAS Cable - Serial Attached SCSI SFF-8088 to SFF-8088

Product ID: ISAS88883



The ISAS88883 3m External SAS Cable is designed for high-performance networks, servers, workstations and desktops, supporting data transfer rates of up to 6 Gbps.

This durable Mini SAS cable features SFF-8088 to SFF-8088 plugs for connecting your external SAS devices (controllers, hard drives, SAN storage area network, etc.), and it is TAA-compliant for Federal (GSA Schedule) purchases.

Constructed of high quality materials this 3-meter SAS cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures
- Connect SAS Controllers to SAS Backplanes
- Connect external hard drive to SAS Controller

### Features

- 2x SFF-8088 plugs with latches
- Durable metal connectors
- Supports data transfer rates up to 6 Gbps
- Multi-lane design
- Backwards compatible with SATA devices

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-polyester foil with tinned copper braid
	Number of Conductors	8 Twisted Pair
<b>Connector(s)</b>	Connector A	1 - SFF-8088 (26-pin, External Mini-SAS) Latching Plug
	Connector B	1 - SFF-8088 (26-pin, External Mini-SAS) Latching Plug
<b>Physical Characteristics</b>	Cable Length	9.8 ft [3 m]
	Color	Black
	Product Length	9.8 ft [3 m]
	Product Weight	0.7 lb [0.3 kg]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	0.7 lb [0.3 kg]
<b>What's in the Box</b>	Included in Package	1 - 3m External Serial Attached SCSI SAS Cable - SFF-8088 to SFF-8088

Product appearance and specifications are subject to change without notice.