

Travel A/V adapter: 3-in-1 Mini DisplayPort to DisplayPort DVI or HDMI converter

Product ID: MDP2DPDVHD



The MDP2DPDVHD mini DisplayPort® to DisplayPort®, DVI or HDMI® Multifunction Adapter converts a mini DisplayPort (mDP®) input to DisplayPort, DVI or HDMI output signals - all in a single compact adapter.

This multifunction adapter offers the unique ability to connect almost any display to your mini DisplayPort equipped PC or Mac, providing the perfect solution for business environments that have mixed display hardware - saving the expense of purchasing new displays for compatibility. This Mini DisplayPort adapter is the perfect accessory for any of your MacBook® or Microsoft® Surface™ Pro devices with mDP.

A plug-and-play solution that requires no software or drivers, this versatile mDP adapter offers a quick and simple installation for the utmost convenience.

Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™ I/O port.

This adapter allows for audio pass-through if supported by the video source. Please review the video source manual to confirm support.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.



Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Use your existing DVI, HDMI® or DisplayPort® monitors with a new mini DisplayPort® device
- Perfect for IT professionals seeking a solution for connecting mixed display hardware to mini DisplayPort computers

Features

- Adapt Mini DisplayPort to DisplayPort, HDMI or DVI
- Supports resolutions up to 2560x1600 using DisplayPort, 1920x1200 using HDMI/DVI
- No software/drivers required
- Compact design
- Compatible with Intel® Thunderbolt™

Hardware	Warranty	3 Years
	Active or Passive Adapter	Passive
	Adapter Style	Adapters
	Audio	Yes
	AV Input	Mini-DisplayPort
	AV Output	DisplayPort DVI HDMI
Performance	Audio Specifications	5.1 Surround Sound
	Maximum Digital Resolutions	DisplayPort: 2560x1600 DVI/HDMI; 1920x1200
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - DisplayPort (20 pin) Female 1 - DVI-D (25 pin) Female 1 - HDMI (19 pin) Female
Environmental	Humidity	10~85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	5.9 in [150 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.6 in [1.5 cm]
	Product Length	9.4 in [24 cm]
	Product Width	1.8 in [45 mm]
	Weight of Product	1.7 oz [47 g]
Packaging Information	Package Height	0.7 in [19 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	2 oz [56 g]
What's in the Box	Included in Package	1 - MDP to DP/DVI/HDMI Adapter

Product appearance and specifications are subject to change without notice.