

Mini DisplayPort to DVI Video Adapter Converter - Black Mini DP to DVI - 1920x1200

Product ID: MDP2DVI3



The MDP2DVI3 Mini DisplayPort® to DVI Adapter lets you connect your Mini DisplayPort video source (such as any of your MacBook® or Microsoft® Surface™ Pro devices with mDP) to a DVI monitor, projector, or display, eliminating the expense of having to upgrade to a Mini DisplayPort-capable monitor.

Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™ I/O port, the adapter supports display or projector resolutions up to 1920x1200 (WUXGA) and is compliant with HDCP standards.

MDP2DVI3 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI® signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your existing DVI monitor to Mini DisplayPort output device
- Ideal for using your DVI monitor as a secondary display

Features

- Easy to use cable-style adapter, with no software required
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal

| | | |
|-------------------------------------|-------------------------------|--|
| Hardware | Warranty | 3 Years |
| | Active or Passive Adapter | Passive |
| | Adapter Style | Adapters |
| | Audio | No |
| | AV Input | DisplayPort |
| | AV Output | DVI |
| Performance | Maximum Digital Resolutions | 1920x1200 / 1080p |
| | Wide Screen Supported | Yes |
| Connector(s) | Connector A | 1 - Mini-DisplayPort (20 pin) Male |
| | Connector B | 1 - DVI-I (29 pin) Female |
| Special Notes / Requirements | System and Cable Requirements | DP++ (DisplayPort++) port required from video card or video source for DVI and HDMI® signal pass-through |
| Environmental | Humidity | 40%-85%RH |
| | Operating Temperature | 0°C to 60°C (32°F to 140°F) |
| | Storage Temperature | 0°C to 70°C (32°F to 158°F) |
| Physical Characteristics | Cable Length | 5.1 in [13 cm] |
| | Color | Black |
| | Product Height | 0.6 in [1.5 cm] |
| | Product Length | 7.3 in [18.5 cm] |
| | Product Width | 1.6 in [40 mm] |
| | Weight of Product | 0.9 oz [26.5 g] |
| Packaging Information | Package Height | 0.8 in [20 mm] |
| | Package Length | 9.4 in [24 cm] |
| | Package Width | 6.3 in [16 cm] |
| | Shipping (Package) Weight | 1.8 oz [51 g] |
| What's in the Box | Included in Package | 1 - Mini DisplayPort® to DVI Adapter |

Product appearance and specifications are subject to change without notice.