

Mini DisplayPort to DVI Dual-Link Active Adapter – USB Powered

Product ID: MDP2DVID



The MDP2DVID Mini DisplayPort to DVI-D Dual-Link adapter lets you connect your Mini DisplayPort video source (such as any of your MacBook® or Microsoft® Surface™ Pro devices with mDP) to any DVI-D display, including televisions and Apple Cinema Display HD, eliminating the expense of having to upgrade to a Mini DisplayPort-capable monitor.

The Mini DisplayPort adapter offers an active conversion, which is powered by a single USB port and is able to handle full dual-link resolutions (up to 2560x1600). Use it to mirror your display to another monitor, or extend your desktop to increase your workspace.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing DVI monitor to be used with your new Mini DisplayPort device
- Perfect for larger format screens that use high DVI resolutions with Dual-Link connectivity
- Ideal for using your DVI monitor as a secondary display

Features

- Maximum resolution up to 2560x1600 with DVI Dual-Link
- Supports 1920x1080 with Single-Link displays
- Support for any DVI-D display, including televisions and Apple Cinema Display HD
- Powered by a single USB 2.0 port
- Simple plug and play installation; no software required

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	Audio	No
	AV Input	Mini-DisplayPort
	AV Output	DVI
	Industry Standards	DisplayPort 1.1a
Performance	Maximum Digital Resolutions	Dual Link: 2560x1600 Single Link: 1920x1200
	Supported Resolutions	2560x1600 @ 60Hz 1920x1200 @ 120Hz 1920x1080 @ 120Hz
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male 1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - DVI-D (25 pin) Female
Power	Power Source	USB-Powered
Environmental	Humidity	10% to 85 % RH (no condensation)
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	24 in [610 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.5 in [1.2 cm]
	Product Length	8.2 in [20.8 cm]
	Product Width	6.3 in [16 cm]
	Weight of Product	4.2 oz [118 g]
Packaging Information	Package Height	0.6 in [16 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	4.5 oz [127 g]
What's in the Box	Included in Package	1 - Mini-Displayport to DVI adapter

1 - Instruction manual

Product appearance and specifications are subject to change without notice.