

10 ft Mini DisplayPort to DVI Adapter Converter Cable – Mini DP to DVI 1920x1200 - White

Product ID: MDP2DVIMM10W



The MDP2DVIMM10W Mini DisplayPort to DVI Adapter Cable lets you directly connect your Mini DP video source (such as any of your MacBook® or Microsoft® Surface™ Pro devices with mDP) to a DVI monitor or projector, eliminating the expense of having to upgrade to a Mini DisplayPort-capable monitor.

The adapter cable is 10 feet (3 m) in length, and features male-to-male connectors, allowing you to connect your Mini DisplayPort source directly to a DVI display with no additional cabling required.

Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt I/O port, the adapter supports resolutions up to 1920x1200 (WUXGA).

MDP2DVIMM10W is a passive adapter that requires a dual-mode DisplayPort port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your existing DVI display device (monitor, projector) to a Mini DisplayPort output device
- Ideal for using your DVI monitor as a secondary display

Features

- 1x Male Mini DisplayPort connector, 1x Male DVI connector
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal

Hardware	Warranty	3 Years
	Active or Passive Adapter	Passive
	Adapter Style	Cable Adapters
	Audio	No
	AV Input	Mini DisplayPort - 1.2
	AV Output	DVI
	Chipset ID	NXP - 3361
Performance	Maximum Cable Length	10 ft [3 m]
	Maximum Digital Resolutions	1920x1200 / 1080p
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
Special Notes / Requirements	System and Cable Requirements	DP++ (DisplayPort++) port required from video card or video source for DVI and HDMI® signal pass-through
Environmental	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	0°C to 70°C (32°F to 158°F)
Physical Characteristics	Cable Length	10 ft [3 m]
	Color	White
	Product Height	0.6 in [1.5 cm]
	Product Length	10 ft [3 m]
	Product Width	1.5 in [37 mm]
	Weight of Product	5.4 oz [154 g]
Packaging Information	Package Height	0.7 in [18 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	0.4 lb [0.2 kg]
What's in the Box	Included in Package	1 - Mini DisplayPort® to DVI Adapter

Product appearance and specifications are subject to change without notice.