

## 6 ft Mini DisplayPort to DVI Active Adapter Converter Cable - mDP to DVI 1920x1200 - White

Product ID: MDP2DVIMM6WS



The MDP2DVIMM6WS 6ft active Mini DisplayPort to DVI adapter cable lets you directly connect your Mini DP video source (Laptop, Macbook®, Ultrabook™ etc.) directly to a DVI monitor or projector, saving the expense of additional adapters. The converter features a stylish white design, that is well-suited for connecting Mac® computers.

For guaranteed compatibility with virtually any Mini DisplayPort output the active Mini DP to DVI adapter supports multimode (DP++) as well as single-mode DisplayPort signals. Unlike passive adapters, this ensures the MDP2DVIMM6WS can be used with graphics cards that are not capable of outputting multimode DP++ signals, such as ATI® Eyefinity cards.

Compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt™ I/O port, the adapter supports resolutions up to 1920 x 1200.

The MDP2DVIMM6WS is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Note:

This adapter is not compatible for use with the Apple Cinema Display.

### Certifications, Reports and Compatibility



### Applications

- Use with single-mode Mini DisplayPort video outputs that are not capable of outputting multimode DP++ signals, such as ATI® Eyefinity video cards
- Connect your DVI display device (monitor, projector) directly to a Mini DisplayPort output device
- Ideal for using your DVI monitor as a secondary display

### Features

- Active Mini DisplayPort to DVI conversion
- 1x Male DisplayPort connector, 1x Male DVI connector
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal
- Supports resolutions up to 1920 x 1200
- Plug-and-play Installation

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Cable Adapters
	Audio	No
	AV Input	DisplayPort
	AV Output	DVI
	Chipset ID	Parade - PS171
<b>Performance</b>	Maximum Cable Length	6 ft [1.8 m]
	Maximum Digital Resolutions	1024 x 768 1280 x 720 1920 x 1080 1920 x 1200
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
<b>Special Notes / Requirements</b>	System and Cable Requirements	Some dual-link DVI monitors manufactured prior to 2014 may have limited resolutions support when used with this adapter.  This adapter is not compatible for use with the Apple Cinema Display.
<b>Environmental</b>	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	6 ft [1.8 m]
	Color	White
	Product Height	0.6 in [15 mm]
	Product Length	6 ft [1.8 m]
	Product Weight	4.6 oz [129.3 g]
	Product Width	1.6 in [40 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	4.3 oz [123 g]
<b>What's in the Box</b>	Included in Package	1 - Active DisplayPort to DVI Adapter

Product appearance and specifications are subject to change without notice.