

## 6 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - Black

Product ID: MDP2VGAMM6B



The MDP2VGAMM6B 6ft active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped device (Desktop PC, Mac®, Laptop, Ultrabook™, etc.) directly to a VGA monitor or projector with no additional adapters or cables required -- a cost-effective solution for enabling your Mini DisplayPort computer to work with a VGA monitor or projector.

The adapter cable is compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM6B is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

### Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Cable Adapters
	Audio	No
	AV Input	Mini-DisplayPort
	AV Output	VGA
	Chipset ID	Analogix - 9832
<b>Performance</b>	Maximum Analog Resolutions	1920x1200 / 1080p (Output)
	Maximum Cable Length	6 ft [1.8 m]
	Maximum Digital Resolutions	1920x1200 / 1080p (Input)
<b>Connector(s)</b>	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Male
<b>Environmental</b>	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Height	0.7 in [19 mm]
	Product Length	72 in [1830 mm]
	Product Weight	3.6 oz [101.3 g]
	Product Width	1.5 in [37 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	4.3 oz [123 g]
<b>What's in the Box</b>	Included in Package	1 - Mini DisplayPort to VGA Adapter Cable

Product appearance and specifications are subject to change without notice.