

1,8m (6 ft) Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

Product ID: MDP2VGAMM6W



The MDP2VGAMM6W 6ft active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped device (such as a Macbook® or any Microsoft® Surface™ Pro devices with mDP) directly to a VGA monitor or projector with no additional adapters or cables required -- a cost-effective solution for enabling your Mini DisplayPort computer to work with a VGA monitor or projector. The cable features a stylish white design, that is well-suited for connecting Mac® computers.

The adapter cable is compatible with Intel® Thunderbolt™, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM6W is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Cable Adapters
	Audio	No
	AV Input	Mini-DisplayPort
	AV Output	VGA
	Chipset ID	Analogix - 9832
Performance	Maximum Analog Resolutions	1920x1200 / 1080p (Output)
	Maximum Cable Length	6 ft [1.8 m]
	Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Male
Environmental	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	White
	Product Height	0.6 in [1.5 cm]
	Product Length	36 in [91.5 cm]
	Product Width	1.6 in [40 mm]
	Weight of Product	3.3 oz [94.6 g]
Packaging Information	Package Height	0.6 in [15 mm]
	Package Length	8.8 in [22.3 cm]
	Package Width	7.8 in [19.8 cm]
	Shipping (Package) Weight	4.2 oz [120 g]
What's in the Box	Included in Package	1 - Mini DisplayPort to VGA Adapter Cable

Product appearance and specifications are subject to change without notice.