

## Travel A/V Adapter: 3-in-1 Mini DisplayPort to VGA DVI or HDMI Converter - White

Product ID: MDP2VGDVHDW



The MDP2VGDVHDW Mini DisplayPort to VGA, DVI or HDMI converter offers a three-in-one solution for connecting an Mini DP video source (such as any of your MacBook® or Microsoft® Surface™ Pro devices with mDP) to a VGA, DVI, or HDMI Display. Ensuring compatibility with almost any display, television or projector, this compact and lightweight adapter offers the ideal plug-and-play solution for travel, or BYOD (Bring Your Own Device) applications around the office.

You can walk into any boardroom and be ready to connect, even if you don't know what connection ports are available. The MDP2VGDVHDW maximizes the audio/video connectivity of your MacBook® by offering three different output ports, in a single compact adapter.

The three-in-one converter is compatible with Intel® Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200/1080p you can convert a Mini DisplayPort video source to VGA, HDMI, or DVI without sacrificing video quality.

The Mini DisplayPort converter requires no power adapter and maximizes portability by easily travelling in your laptop bag with a small footprint and lightweight design.

The MDP2VGDVHDW features a sleek white design that looks great next to your MacBook® Pro or MacBook Air®, and is backed by a 3-year StarTech.com warranty and free lifetime technical support.



### Certifications, Reports and Compatibility



### Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work
- Connect a DVI, VGA, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

### Features

- Three-in-one adapter - mDP to: VGA, DVI, HDMI
- Support for video resolution up to 1920x1200/1080p
- Plug-and-play installation
- Compatible with Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal
- Small footprint
- Portable, lightweight construction
- Sleek White Design

<b>Hardware</b>	Warranty	3 Years
	Active or Passive Adapter	Active
		Passive
	Adapter Style	Adapters
	Audio	Yes
	AV Input	Mini-DisplayPort
	AV Output	DVI
HDMI		
VGA		
<b>Performance</b>	Audio Specifications	5.1 Surround Sound (Video source and destination dependant)
	Maximum Analog Resolutions	1920x1200/1080p
	Maximum Digital Resolutions	1920x1200/1080p
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - HDMI (19 pin) Female
		1 - VGA (15 pin, High Density D-Sub) Female
		1 - DVI-D (25 pin) Female
<b>Special Notes / Requirements</b>	<b>Note</b>	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
		The HDMI port is a passive port. The DVI-D is a passive port. The VGA port is an active port.
<b>Environmental</b>	Humidity	10~85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
<b>Physical Characteristics</b>	Cable Length	5.9 in [150 mm]
	Color	White
	Product Height	0.6 in [1.5 cm]
	Product Length	10.6 in [27 cm]
	Product Width	1.8 in [45 mm]
	Weight of Product	2 oz [57 g]

<b>Packaging Information</b>	Package Height	0.8 in [20 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	2.3 oz [66 g]
<b>What's in the Box</b>	Included in Package	1 - Mini DisplayPort to HDMI/VGA/DVI Adapter 1 - Installation Guide

Product appearance and specifications are subject to change without notice.