

Aluminum Travel A/V Adapter: 3-in-1 Mini DisplayPort to VGA, DVI or HDMI - 4K

Product ID: MDPVGDVHD4K



This 3-in-1 travel adapter offers a portable solution for connecting your Mini DisplayPort computer to a VGA, DVI or HDMI® display.

The adapter is VESA certified, to ensure compatibility with your mDP computer.



Stylish connectivity for MacBook Pro and MacBook Air

This travel adapter has been constructed with a sturdy aluminum housing and features a pure white Mini DisplayPort cable built in. While the adapter looks great and works well with any mDP device, it's designed to seamlessly match your MacBook Air or MacBook Pro.



All-in-one video connectivity, with travel in mind

Instead of filling your laptop bag with different converters for different displays, this 3-in-1 adapter gives you all the video outputs you'll need. With VGA, DVI and HDMI outputs, this adapter lets you connect from your laptop's Mini DisplayPort port to any boardroom or classroom display, without the inconvenience of carrying a separate adapter for each display type.

With support for multiple video outputs and a lightweight, small-footprint design, this adapter is the ideal plug-and-play solution for travel or BYOD (Bring Your Own Device) applications around the office.

Innovative, built-in cable manager

The adapter features a built-in magnetic fastener, for cable management. The magnet helps guide the breakout cable into place for quick and secure storage while traveling, ensuring the adapter is neatly stored in your travel bag.

Astonishing picture quality with support for Ultra HD 4K

The HDMI output on this adapter supports Ultra HD 4K resolutions, providing four times the picture quality of high-definition 1080p. The HDMI output is also backward compatible with lower resolutions, such as 1080p and 720p, so the adapter is also perfect for your legacy video equipment. The VGA and DVI outputs also support a high-definition maximum resolution up to 1920 x 1200, so you can still enjoy excellent video quality.

The travel adapter is compatible with mDP Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal.

The MDPVGDVHD4K is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD MacBook Pro or MacBook Air to a provided VGA, DVI, or HDMI display at work
- Connect a VGA, DVI, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

Features

- 3-in-1 adapter - mDP to VGA, mDP to DVI and mDP to HDMI
- Maximum portability with built-in magnetic cable manager
- Astonishing picture quality with support for UHD 4K
- Compatible with mDP Intel® Thunderbolt™ devices that are capable of outputting a DisplayPort signal
- VESA certified
- Plug-and-play installation
- Small footprint
- Lightweight design

Hardware	Warranty	3 Years
	Adapter Style	Adapters
	Audio	Yes
	AV Input	Mini-DisplayPort
	AV Output	DVI HDMI VGA
Performance	Audio Specifications	HDMI output - 7.1 surround sound
	General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
	Maximum Analog Resolutions	1920 x 1200
	Maximum Digital Resolutions	3840 x 2160
	Supported Resolutions	HDMI output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720 DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
	Video Revision	DisplayPort 1.2
Wide Screen Supported	Yes	
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male Input
	Connector B	1 - HDMI (19 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-D (25 pin) Female Output
Special Notes / Requirements	Note	The HDMI port is a passive port. The DVI-D is a passive port. The VGA port is an active port.
Environmental	Humidity	40%-50%RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Accent Color	White
	Cable Length	4.3 in [110 mm]
	Color	Silver
	Product Height	0.6 in [1.5 cm]

	Product Length	4.1 in [10.3 cm]
	Product Width	2.2 in [55 mm]
	Weight of Product	4.3 oz [121 g]
Packaging Information	Package Height	1.3 in [32 mm]
	Package Length	5.8 in [14.7 cm]
	Package Width	6.8 in [17.3 cm]
	Shipping (Package) Weight	6.3 oz [179 g]
What's in the Box	Included in Package	1 - travel A/V adapter

Product appearance and specifications are subject to change without notice.