

## 30,4m (100 ft.) Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101HQ\_100



This 100ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### Certifications, Reports and Compatibility



### Applications

- Extends your VGA monitor cable

### Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

<b>Connector(s)</b>	Warranty	Lifetime
	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
<b>Special Notes / Requirements</b>	<b>Note</b>	Pin number 9 is not populated on these connectors
<b>Physical Characteristics</b>	Cable Length	100 ft [30.5 m]
	Color	Black
	Product Length	100 ft [30.5 m]
	Product Weight	6.2 lb [2.8 kg]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Shipping (Package) Weight	7.2 lb [3.3 kg]
<b>What's in the Box</b>	Included in Package	1 - 100 FOOT COAXIAL CABLE
		2 - Nuts

Product appearance and specifications are subject to change without notice.