

## 6 ft Monitor VGA Cable - HD15 M/M

Product ID: MXT101MM



This 6-foot VGA Video Monitor Cable features two HDDB15 (male) connectors, providing a high quality VGA connection.

**The cable supports a maximum video resolution of up to 800x600.** For applications that require higher resolutions, see our [6ft Coax VGA Cable](#) (MXT101MMHQ).

The MXT101MM is backed by StarTech.com's lifetime warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

### Features

- Supports video resolutions up to 800x600
- Guaranteed reliability

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Connector(s)</b>	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Male
<b>Special Notes / Requirements</b>	<b>Note</b>	Pin number 9 is not populated on these connectors Supports resolutions up to 800x600
<b>Physical Characteristics</b>	Cable Length	6 ft [1.8 m]
	Color	Gray
	Product Height	0.7 in [1.8 cm]
	Product Length	6 ft [1.8 m]
	Product Width	1.3 in [33 mm]
	Weight of Product	4.3 oz [122 g]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	0.5 in [13 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	4.5 oz [127 g]
<b>What's in the Box</b>	Included in Package	1 - 6 ft VGA Monitor Cable - HD15 M/M

Product appearance and specifications are subject to change without notice.