

10 ft VGA Monitor Cable - HD15 MM

Product ID: MXT101MM10



This 10-foot VGA Video Monitor Cable features two HDDB15 (male) connectors, providing a high quality VGA connection.

The cable supports a maximum video resolution of up to 800x600. For applications that require higher resolutions, see our [10ft Coax VGA Cable](#) (MXT101MMHQ10).

The MXT101MM10 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

Features

- Supports video resolutions up to 800x600
- Guaranteed reliability

	Warranty	Lifetime
Hardware	Connector Plating	Nickel
Connector(s)	Connector A	VGA (15 pin, High Density D-Sub) Male
	Connector B	VGA (15 pin, High Density D-Sub) Male
Special Notes / Requirements	Note	Pin number 9 is not populated on these connectors Supports resolutions up to 800x600
Physical Characteristics	Cable Length	10 ft [3 m]
	Color	Gray
	Product Length	10 ft [3 m]
	Product Weight	14.5 oz [412.1 g]
Packaging Information	Shipping (Package) Weight	14.7 oz [417.1 g]
What's in the Box	Included in Package	1 - 10 ft VGA Monitor Cable - HD15 MM

Product appearance and specifications are subject to change without notice.