

15 ft Monitor VGA Cable - HD15 MM

Product ID: MXT101MM15



This 15-foot VGA Video Monitor Cable features two HDDB15 (male) connectors, providing a high quality VGA connection.

The cable supports a maximum video resolution of up to 800x600. For applications that require higher resolutions, see our [15ft Coax VGA Cable](#) (MXT105MMHQ).

The MXT101MM15 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

Features

- Supports video resolutions up to 800x600
- Guaranteed reliability

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Connector(s)	Connector A	VGA (15 pin, High Density D-Sub) Male
	Connector B	VGA (15 pin, High Density D-Sub) Male
Special Notes / Requirements	Note	Pin number 9 is not populated on these connectors Supports resolutions up to 800x600
Physical Characteristics	Cable Length	15 ft [4.6 m]
	Color	Gray
	Product Height	15.000
	Product Length	15 ft [4.6 m]
	Product Width	33.000
	Weight of Product	8.2 oz [231.5 g]
	Wire Gauge	28 AWG
Packaging Information	Package Height	0 in [0.1 mm]
	Package Length	11.4 in [29 cm]
	Package Width	5.7 in [14.5 cm]
	Shipping (Package) Weight	8.4 oz [239 g]
What's in the Box	Included in Package	1 - 15 ft VGA Monitor Cable HD15 MM

Product appearance and specifications are subject to change without notice.