

18in Coax High Resolution VGA Monitor Cable - HD15 M/M

Product ID: MXTMMHQ18IN



This 18in High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, this high resolution VGA (SVGA) cable features two HD15 male connectors and provides a connection distance of 18in.

Certifications, Reports and Compatibility



Features

- Ideal for high resolution monitors (1024x768 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Connector(s)	Warranty	Lifetime
	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Male
Physical Characteristics	Cable Length	18 in [457.2 mm]
	Color	Black
	Product Length	18 in [457.2 mm]
	Weight of Product	4.1 oz [116 g]
Packaging Information	Package Height	8.3 in [21.2 cm]
	Package Length	7.8 in [19.9 cm]
	Package Width	0.6 in [16 mm]
	Shipping (Package) Weight	4.1 oz [116 g]

Product appearance and specifications are subject to change without notice.