

5m Coax High Resolution Monitor VGA Video Cable - HD15 to HD15 M/M

Product ID: MXTMMHQ5M



The MXTMMHQ5M High Resolution VGA Cable (5-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Create a longer connection between a high resolution VGA display and a desktop PC/video switch than a typical cable length would allow

Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	14
	Number of Ferrites	1
Connector(s)	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Male
Environmental	Humidity	0 - 80 %RH
	Operating Temperature	0 to 60 °C
	Storage Temperature	-20 to 80 °C
Physical Characteristics	Cable Length	5 m [16.4 ft]
	Color	Black
	Product Length	5 m [16.4 ft]
	Product Weight	0.6 kg [1.2 lb]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	0.6 kg [1.2 lb]
What's in the Box	Included in Package	1 - 5m Coax High Resolution Monitor VGA Cable - HD15 M/M

Product appearance and specifications are subject to change without notice.