

## 4 Port PCI Express Low Profile High Speed USB Card

Product ID: PEXUSB4DP



The PEXUSB4DP is a low profile 4 port USB card designed for versatility and performance.

Providing simple system expansion for added peripheral connections, this PCI Express USB card adds 3 external USB 2.0 slots and 1 internal USB 2.0 slot, with support for high speed USB 2.0 data transfer rates of up to 480 Mbps, and includes WHQL certified drivers and easy plug and play installation.

Capable of adapting to virtually any PC case form factor, the low profile USB card includes a standard profile bracket for installation in full form factor cases.

### Certifications, Reports and Compatibility



### Applications

- Add USB 2.0 connectivity to any PCIe based desktop, workstation or server
- Expand on a computers USB 2.0 capabilities with 4 additional ports for more USB device connections
- Add an internal USB port to connect internal or front-bay mounted USB devices
- Connect additional external hard drives, CD/DVD drives, MP3 players, printers, scanners, webcams, game controllers, digital cameras, etc. to a computer system

### Features

- 3 external and 1 internal USB 2.0 port
- High Speed USB 2.0 compliant, with transfer rates up to 480Mbps
- Backward compatible with USB 1.0/1.1 devices
- Provide up to 500mA of power per port with dedicated power input
- Plug-and-Play compatible
- Includes a full profile installation bracket

<b>Hardware</b>	Warranty	2 Years
	Bus Type	PCI Express
	Card Type	Low Profile (SP bracket incl.)
	Chipset ID	VIA/VLI - VT6212
	Industry Standards	PCI Express One Lane 2.5Gb/s
	Interface	USB 2.0
	Ports	4
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector Type(s)	1 - PCI Express x1 Male
	External Ports	3 - USB Type-A (4 pin) USB 2.0 Female
	Internal Ports	1 - SP4 (4 pin, Small Drive Power) Male 1 - USB Type-A (4 pin) USB 2.0 Female
<b>Software</b>	OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016, 2019 Mac OS X® 10.6 to 10.10 Linux 3.5.x to 4.11.x <i>LTS versions only</i>
<b>Special Notes / Requirements</b>	System and Cable Requirements	PCI Express enabled computer with an available PCI Express x1 slot or higher
<b>Environmental</b>	Humidity	80% RH
	Operating Temperature	-0°C to 75°C (32°F to 167°F)
	Storage Temperature	-40°C to 125°C (-40°F to 257°F)
<b>Physical Characteristics</b>	Product Height	0.8 in [2 cm]
	Product Length	3.5 in [90 mm]
	Product Width	3.1 in [80 mm]
	Weight of Product	1.6 oz [46 g]
<b>Packaging Information</b>	Package Height	1.3 in [32 mm]
	Package Length	5.7 in [14.4 cm]
	Package Width	6.9 in [17.4 cm]
	Shipping (Package) Weight	4.7 oz [132 g]
<b>What's in the Box</b>	Included in Package	1 - PCI Express USB 2.0 Card 1 - Full Profile Bracket 1 - Driver CD

Product appearance and specifications are subject to change without notice.