

# 12U Slide-Out Server Rack - Rotating - 4-Post Rack

Product ID: PORACK12U



This 12U slide-out server rack helps you save space while keeping your rack-mount equipment organized and accessible. The compact open-frame rack is easy to pull out and rotate, which makes it easy to install and access your equipment or perform maintenance when needed.

The rack supports a total load capacity of 125 lb. (56.7 kg).

## **Save space in your office or server room**

The rack helps you save valuable floor space. It's designed for installation in small areas such as below a table or in a cabinet or cupboard. Its versatility makes this the perfect rack for storing your servers in a boardroom, small office/home office, restaurant or any place where space is at a premium.

## **Keep your equipment cool and accessible**

For easy equipment installation and maintenance, the 12U server rack's base is on sliding rails, which means it's easier to access the back of your equipment. With its open-frame design, the rack not only maximizes accessibility but also offers unobstructed airflow to your equipment, providing passive cooling to keep your rack-mounted equipment running at optimal temperatures.

**Save money on shipping**

The rack comes in a flat-packed box, which reduces shipping volume and significantly lowers cost when compared to racks that ship fully assembled. Plus, because the rack is packaged efficiently, it's easy to transport and store.

The PORACK12U is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

### Features

- Slide-out design lets you manage your rack-mounted equipment easily
- Comes in a flat-pack, making it easy to transport and reducing shipping costs
- Open frame provides passive cooling for equipment
- Store your servers out of the way in a cabinet or cupboard

<b>Hardware</b>	Warranty	2 Years
	Cable Management	Yes
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Special Features	Built-in Cable Management Easy Assembly U-Markings
	U Height	12U
	Wallmountable	No
<b>Performance</b>	Weight Capacity	125.3 lb [56.7 kg]
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
<b>Product Measurements</b>	Maximum Mounting Depth	16.7 in [42.5 cm]
	Product Height	24.2 in [61.5 cm]
	Product Length	22.4 in [56.8 cm]
	Product Width	19.2 in [48.7 cm]
	Weight of Product	51.6 lb [23.4 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Package Height	8.7 in [22 cm]
	Package Length	24.6 in [62.5 cm]
	Package Width	21.7 in [55 cm]
	Shipping (Package) Weight	58.7 lb [26.6 kg]
<b>What's in the Box</b>	Included in Package	1 - Sliding Tray 1 - Top Bracket 6 - Vertical Rails 1 - Stabilizing Plate 1 - Security Plate

4 - Narrow Cable Managers

1 - Cable Manager

2 - Thumbscrews

24 - Assembly Screws

24 - Assembly Nuts

48 - M5 Cage Nuts

48 - M5 Screws

1 - User Manual

---

Product appearance and specifications are subject to change without notice.