

Wireless Presentation Remote with Red Laser Pointer - 90 ft. (27 m)

Product ID: PRESREMOTE



This wireless presentation remote helps you deliver seamless presentations by combining intuitive navigation and a laser pointer in a single compact unit.

Engage Your Audience

Being confined to your computer isn't the most effective way to deliver a presentation, especially when you're trying to engage your audience. This presentation clicker has a wireless range of 90 ft. (27 m) so you have control of what's on your screen with the freedom to move around the room while controlling your presentation as if you were at your computer.

Point Out Key Messages

With a built-in red laser pointer, this presentation remote lets you guide your audience's attention to critical information in your content. It's also perfect for use as a slide advancer in PowerPoint® presentations, websites or any other documents you want to share with your audience.

Present from Anywhere

This wireless presentation clicker features a sleek, ergonomic design and includes the required batteries along with a protective carrying case, for total portability. You can store the wireless receiver inside the presentation remote when you're not using it.

The USB receiver works with virtually any Mac or Windows computer. Simply plug the receiver into your laptop and you're ready to present.

PRESREMOTE is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control your PowerPoint presentation with easy-to-use buttons
- Highlight critical information with the red laser pointer
- Freely move around the room while you present

Features

- Engage your audience, move freely around the room, with a wireless range of up to 90 ft. (27 m)
- Easily control your presentation with intuitive push-button operation and no additional software or drivers required
- Draw your audience's attention to specific on-screen content, using the built-in laser pointer
- Protective storage case and batteries included so you can present on the go
- Features a sleek, ergonomic design

Performance	Warranty	2 Years
	Max Distance	27 m / 90 ft
	Optical Power	1mW
	WAVELENGTH	650+20 mm
	Wireless Band	2.4 GHz
Special Notes / Requirements	Note	This is a class 2 laser product
Environmental	Humidity	30%~80% RH
	Operating Temperature	5°C to 45°C (41°F to 113°F)
	Storage Temperature	5°C to 45°C (41°F to 113°F)
Physical Characteristics	Color	Black
	Product Height	1 in [2.5 cm]
	Product Length	5.3 in [13.4 cm]
	Product Width	1.2 in [31 mm]
	Weight of Product	4.2 oz [120 g]
Packaging Information	Package Height	1.7 in [44 mm]
	Package Length	7.7 in [19.5 cm]
	Package Width	3.9 in [98 mm]
	Shipping (Package) Weight	6.4 oz [180 g]
What's in the Box	Included in Package	1 - Presentation Remote
		2 - AAA Batteries
		1 - Carrying Case
		1 - User Manual

Product appearance and specifications are subject to change without notice.