

25 ft Standard Computer Power Cord - NEMA5-15P to C13

Product ID: PXT10125



The PXT10125 25-foot Computer Power Cord is a durable, universal power cord that can be used as a cost effective replacement for your existing PC power cord, and offers 25ft of connection distance between a computer or peripheral device and an available power outlet - an ideal solution for connecting your monitor, PC or laser printer to a grounded power outlet.

Backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Plugs monitor, PC, or laser printer into a grounded power outlet

Features

- One NEMA 5-15 plug and one C13 Receptacle rated to carry 125V at 10A

Hardware	Warranty	Lifetime
	Cable Type	SVT
	Number of Conductors	3
Connector(s)	Connector A	1 - NEMA 5-15 Power (North America) Plug
	Connector B	1 - IEC 60320 C13 Power
Special Notes / Requirements	Note	UL Listed
Power	Input Current	10A
	Input Voltage	125 AC
Physical Characteristics	Cable Length	25 ft [7.6 m]
	Color	Black
	Product Height	1 in [2.5 cm]
	Product Length	25 ft [7.6 m]
	Product Width	1 in [25 mm]
	Weight of Product	17 oz [481 g]
	Wire Gauge	18 AWG
Packaging Information	Package Height	2.2 in [55 mm]
	Package Length	8.7 in [22 cm]
	Package Quantity	1
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	17.3 oz [490 g]
What's in the Box	Included in Package	1 - 25 ft Standard Computer Power Cord - NEMA5-15P to C13

Product appearance and specifications are subject to change without notice.