

## 3 ft 14 AWG Computer Power Cord - IEC C14 to IEC C15

Product ID: PXTC14C153



The PXTC14C153 C14 to C15 Power Cord (3 ft) features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to C14 Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this C14 to C15 power cable is backed by our Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect large server applications to PDUs located in high-temperature environments
- Compatible with Cisco, HP and other hardware devices with C15 power connections

### Features

- 1x IEC 60320 C15 connector
- 1x IEC 60320 C14 connector
- Rated to carry 250V at 15A
- 14 AWG wire
- UL, RoHS Compliant
- Fully molded strain relief connectors
- Temperature Rating of 105°C

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Type	SJT
	Number of Conductors	3
<b>Connector(s)</b>	Connector A	1 - IEC 60320 C14 Power
	Connector B	1 - IEC 60320 C15 Power
<b>Power</b>	Input Current	15 A
	Input Voltage	250 AC
<b>Physical Characteristics</b>	Cable Length	3 ft [0.9 m]
	Color	Black
	Product Height	0.8 in [20.5 mm]
	Product Length	3 ft [0.9 m]
	Product Weight	6.4 oz [181 g]
	Product Width	1.1 in [28.5 mm]
	Wire Gauge	14 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	6.6 oz [186 g]
<b>What's in the Box</b>	Included in Package	1 - 3ft Computer Power Cord 14 AWG - C14 to C15

Product appearance and specifications are subject to change without notice.