

Computer power cord - C19 to C20, 14 AWG, 3 ft

Product ID: PXTC19C20143

This C19 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high power connections, making it perfect for server application and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 3 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the PXTC19C20143 power cord is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 3 feet

Features

- Rated to carry 250V at 15A
- 14 AWG wire
- UL, RoHS compliant

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Type	SJT
	Number of Conductors	3
Connector(s)	Connector A	1 - IEC 60320 C19 Power
	Connector B	1 - IEC 60320 C20 Power
Special Notes / Requirements	Note	UL Listed
Power	Input Current	15 A
	Input Voltage	250 AC
Physical Characteristics	Cable Length	3 ft [0.9 m]
	Color	Black
	Product Length	3 ft [0.9 m]
	Product Weight	8 oz [228 g]
	Wire Gauge	14 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	8.3 oz [234 g]
What's in the Box	Included in Package	1 - 3 ft 14 AWG Computer Power Cord - C19 to C20

Product appearance and specifications are subject to change without notice.