

## Hospital-Grade Power Cord - NEMA 5-15P to C13 - 15 ft.

Product ID: PXTMG10115



This NEMA 5-15P to C13 power cord features a hospital-grade plug that lets you connect your computer, monitor or other lab equipment to a hospital-grade AC power outlet.

The NEMA 5-15P-HG plug has been tested to UL and CSA standards in order to protect patients and medical staff against faulty ground connections that can be caused by frequent and abrupt connects and disconnects.

The power cord is built to withstand the demands of a hospital environment and is a dependable and safe replacement for worn out or missing power cords.

The PXTMG10115 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Plug your computer, monitor and other medical equipment with a C14 port to a hospital-grade AC power outlet

### Features

- Hospital-grade NEMA-5-15P plug marked with the Green Dot
- Safe for use in hospitals and medical environments
- Tested to UL 817 and CAN/CSA C22.2 no. 21-14
- Dependable replacement or spare computer power cord
- Rated to carry 125V at 10A

<b>Hardware</b>	Warranty	Lifetime
	Cable Type	SVT
	Number of Conductors	3
<b>Connector(s)</b>	Connector A	1 - NEMA 5-15 Power (North America) Plug
	Connector B	1 - IEC 60320 C13 Power Receptacle
<b>Special Notes / Requirements</b>	<b>Note</b>	UL Listed
<b>Power</b>	Input Current	10 A
	Input Voltage	125 AC
<b>Physical Characteristics</b>	Cable Length	15 ft [4.6 m]
	Color	Black
	Connector Style	Straight
	Product Height	1.3 in [3.3 cm]
	Product Length	15 ft [4.6 m]
	Product Width	1.3 in [32.5 mm]
	Weight of Product	12.1 oz [344 g]
	Wire Gauge	18 AWG
<b>Packaging Information</b>	Package Height	1.2 in [30 mm]
	Package Length	10.6 in [27 cm]
	Package Width	5.1 in [13 cm]
	Shipping (Package) Weight	12.4 oz [351 g]
<b>What's in the Box</b>	Included in Package	1 - NEMA 5-15P to C13 power cord

Product appearance and specifications are subject to change without notice.