

12U Sideways Wall-Mount Rack for Servers

Product ID: RK1219SIDEM



The RK1219SIDEM Wall Mount/Side Mount Deep Open Frame Rack/Cabinet (12U, 19in Wide) lets you mount your servers, A/V or network equipment facing perpendicular to the wall for easy access to mounted devices and equipment. The cabinet/rack features open access to both the front and back of your devices, making it easy to adjust cabling, view LEDs and access configuration buttons as needed; plus, the nature of the sidemount configuration allows for deeper mounting depths than typical wallmount racks. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality SPCC cold-rolled steel, for strength and durability, the open frame equipment rack allows for maximum airflow while still supporting a maximum weight capacity of 159 kg (350 lbs). The wall mount rack also ships complete with all of the M5 screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

Features

- Wall mount holes are 16" from center-to-center, for mounting to any standard wooden studs (easily mounts to concrete or steel as well)
- Package includes all necessary screws/nuts for mounting equipment
- TAA compliant for GSA Schedule purchases
- Mounts equipment facing perpendicular to the wall
- Sturdy SPCC cold-rolled steel construction
- Open frame design for optimum airflow
- Ships fully assembled and ready to use

Hardware	Warranty	Lifetime
	Adjustable Mounting Rails	No
	Cable Management	No
	Casters	No
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA-310-D EIA RS310-D
	Ladder Offset	0.7 in [18 mm]
	Ladder Type	L-Shape
	Mounting Holes	Square
	Mounting Options	Front Mount (Front and Rear)
	Number and Type of Included Cage Nuts	48 - M5
	Rack Type	4-Post
	Tools Included	No
	U Height	12U
	U Markings	No
	Wallmountable	Yes
	Performance	Weight Capacity (Stationary)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Internal Width	21 in [533 mm]
	Minimum Mounting Depth	20.8 in [529 mm]
	Product Height	25.9 in [659 mm]
	Product Length	22.3 in [566 mm]
	Product Weight	46.7 lb [21.1 kg]
	Product Width	21.2 in [538 mm]
Rail Thickness	0.1 in [2 mm]	
Packaging Information	Flat Pack (Assembly Required)	No

	Shipping (Package) Weight	54.6 lb [24.7 kg]
What's in the Box	Included in Package	1 - 12U Rack
		48 - M5 Screws
		48 - M5 Cage Nuts

Product appearance and specifications are subject to change without notice.