

12U Hinged Open Frame Wall-Mount Server Rack - 22 in. Deep

Product ID: RK1219WALLOH



The RK1219WALLOH 12U 22in Depth Hinged Open Frame Wall Mount Server Rack lets you wall mount your (19-inch wide) servers, A/V or network equipment and features a hinged rack design that allows the entire frame to swing open for easy installation and maintenance of your equipment.

The 12U wallmount rack offers a 4 post design for additional support of your equipment, storing a maximum weight capacity of 63 kg (140 lbs). Constructed of high-quality SPCC cold-rolled steel for strength and durability, the open frame wallmount server rack allows for maximum airflow, and ships complete with all of the rack screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

Features

- 12U Hinged Wall Mount Rack
- Hinged design for easy access to rear panels
- TAA compliant for GSA Schedule purchases
- Package includes all necessary screws/nuts for mounting rack equipment
- Open frame design provides additional airflow
- 4 Post design for added stability
- Sturdy SPCC cold-rolled steel construction

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	Special Features	Ships Fully Assembled
		Wall-Mountable
	U Height	12U
Wallmountable	Yes	
Performance	Weight Capacity	140 lb [63.4 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Maximum Mounting Depth	19.8 in [50.2 cm]
	Product Height	25.5 in [64.7 cm]
	Product Length	23.6 in [60 cm]
	Product Width	21.9 in [55.6 cm]
	Weight of Product	39 lb [17.6 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	28.3 in [71.8 cm]
	Package Length	26 in [66 cm]
	Package Width	25 in [63.5 cm]
	Shipping (Package) Weight	45.7 lb [20.7 kg]
What's in the Box	Included in Package	1 - Hinged Wall Mount Rack
		48 - #10-32 UNF Panel Screws
		48 - #10-32 UNF Cage Nuts
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.