

Refurbished 12U 19in Wall Mounted Server Rack Cabinet

Product ID: RK1219WALLR



Refurbished cabinets may have minor scratches and dents similar to photos.

This refurbished 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

Certifications, Reports and Compatibility



Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Data centers
- Industrial control centers
- Telecommunication closets
- Audio/Visual control centers

Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Tempered, vented, lockable glass front door

| | | |
|---------------------------------|-------------------------------|--|
| Hardware | Warranty | 0 Years |
| | Fan Options | Two Optional Fans: 120 mm |
| | Frame Type | Enclosed Cabinet |
| | Front Door Construction | Steel with Glass Window |
| | Front Door Features | Secure Key Lock with Reversible and Removable Front Door |
| | Industry Standards | EIA/ECA-310-E |
| | Mounting Hole Types | Square (For Cage Nut) |
| | Mounting Rail Profile | L-Shape |
| | Rack Type | 4-Post |
| | Rear Door Construction | Steel |
| | Side Panel Construction | Steel |
| | Side Panel Features | Secure Key Lock with Removable Side Panels |
| | Special Features | Adjustable Mounting Rails |
| | | Grounding Lug(s) |
| | Ships Fully Assembled | |
| | Wall-Mountable | |
| | U Height | 12U |
| | Wallmountable | Yes |
| Performance | Weight Capacity | 132.6 lb [60 kg] |
| Physical Characteristics | Color | Beige |
| Product Measurements | Internal Depth | 23.3 in [59.1 cm] |
| | Internal Width | 23.4 in [59.5 cm] |
| | Maximum Mounting Depth | 21.7 in [55 cm] |
| | Minimum Mounting Depth | 0.4 in [1.1 cm] |
| | Product Height | 25.1 in [63.7 cm] |
| | Product Length | 24.2 in [61.4 cm] |
| | Product Width | 23.7 in [60.1 cm] |
| | Weight of Product | 66.3 lb [30 kg] |
| Packaging Information | Flat Pack (Assembly Required) | No |
| | Package Height | 25.8 in [65.6 cm] |

| | | |
|--------------------------|---------------------------|---|
| | Package Length | 27.6 in [70 cm] |
| | Package Width | 27.2 in [69.1 cm] |
| | Shipping (Package) Weight | 68.5 lb [31 kg] |
| What's in the Box | Included in Package | 1 - 19in Cabinet 1 - Keys 1 - Package of Cab screws and Cage Nuts |

Product appearance and specifications are subject to change without notice.