

# 12U Server Rack Cabinet - 30 in. Deep Enclosure

Product ID: RK1233BKM



This server rack provides 12U of storage space in a sleek, secure cabinet for storing standard 19" rack-mount devices such as Dell, HP and IBM servers, along with telecommunication and A/V equipment. The rack is compatible with EIA-310 compliant equipment and supports a total load capacity of 450 kg (992 lb.).

## Hassle-free equipment installation

This rack includes a variety of features that enable you to easily incorporate plenty of equipment. With adjustable mounting rails, you can easily change the rail depth from 3" up to 30.7" (76.2 mm - 780 mm) to ensure compatibility your standard rack-mount equipment. The added depth also provides support for additional cable and power management behind your equipment. For hassle-free cable management, the rack includes a 3 meter roll of hook-and-loop cable tie that makes it easy to keep your cables neat and tidy by binding them together or binding them to the rack. The self-gripping fabric can be cut to any size, enabling a wrap-around solution for the cables of any rack-mount equipment.

The rack features holes with covers on the ceiling and floor panels that make it easy to run cabling to the inside and outside of the cabinet, for discreet cable management. The rack also features grounding lugs that enable you to ground your equipment for added protection. This rack also includes a 1U shelf that gives you a stable surface for placing equipment that's not rack-mountable or storing your tools.

To provide hassle-free deployment, the rack ships fully assembled.

### **Securely protect your equipment**

To keep your rack-mounted equipment secure, this rack features front and rear locking mesh doors. The mesh doors look great in any server room and help provide passive cooling. The doors are also reversible, which gives you the freedom to choose which side of the rack the door opens from, to suit your server room's spatial requirements.

The rack also has removable side panels with independent quick-release locks that enable you to access your equipment easily, while still keeping it secure.

### **Maximum maneuverability, with casters included**

The cabinet features casters for hassle-free access to rear-mounted equipment while providing ease of mobility around your office, studio or server room. Plus, the width and height of the rack fit through standard doorways, giving you the freedom to wheel your server rack into different rooms.

The RK1233BKM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Deploy in technology shops and repair centers that have limited space but tend to have mountable equipment that requires security
- Install rack-mount servers, KVM switches, networking equipment and cabinet consoles
- House rack-mount audio/video equipment for broadcasting in your editing room or television studio

### Features

- Easy rack-mount equipment installation
- Keep your rack-mount equipment secure with lockable doors
- Keep your equipment at an optimal temperature with passive cooling
- Mount equipment at the top of the rack with a ceiling panel that features square venting holes that are cage nut compatible
- Front and side mounting holes to accommodate different types of equipment
- 1U shelf and hook-and-loop cable tie included
- Pre-assembled with protective covers for easy deployment

<b>Hardware</b>	Warranty	5 Years
	Fan Options	Four Optional Fans: 120 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel Mesh
	Front Door Features	Secure Key Lock with Reversible and Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Rear Door Construction	Steel Mesh
	Side Panel Construction	Steel Mesh
	Side Panel Features	Secure Key Lock with Removable Side Panels
	Special Features	Adjustable Mounting Rails
		Built-in Cable Management
Casters (Included)		
Grounding Lug(s)		
Leveling Feet		
	Ships Fully Assembled	
	U-Markings	
	U Height	12U
	Wallmountable	No
<b>Performance</b>	Weight Capacity (Stationary)	994.5 lb [450 kg]
<b>Special Notes / Requirements</b>	<b>Note</b>	Includes CABSHELFV1U and 2 pairs of keys
<b>Physical Characteristics</b>	Color	Black
	Rear Door Features	Secure Key Lock with Reversible and Removable Back Door
<b>Product Measurements</b>	Internal Depth	33.5 in [85.2 cm]
	Internal Width	23.4 in [59.5 cm]
	Maximum Mounting Depth	30 in [76.2 cm]
	Minimum Mounting Depth	2.8 in [7 cm]
	Product Height	25.2 in [64 cm]

	Product Height with Casters	28.1 in [71.3 cm]
	Product Length	33.6 in [85.4 cm]
	Product Width	23.6 in [60 cm]
	Weight of Product	112.3 lb [50.8 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Package Height	33.5 in [85 cm]
	Package Length	35.8 in [90.9 cm]
	Package Width	25 in [63.5 cm]
	Shipping (Package) Weight	124.3 lb [56.2 kg]
<b>What's in the Box</b>	Included in Package	1 - 10 ft. Hook and Loop 1 - 1U Fixed Shelf 1 - Enclosure Cabinet 2 - Door Keys 2 - Side Panel Keys 50 - M6 Cage Nuts 50 - M6 Screws

Product appearance and specifications are subject to change without notice.