

25U Server Rack Cabinet - 37 in. Deep Enclosure

Product ID: RK2537BKM



This 25U server rack provides a sleek, secure cabinet for storing standard 19" rack-mount devices such as Dell, HP, and IBM servers, along with telecommunication and A/V equipment. The rack is compatible with EIA-310 compliant equipment and supports a total load capacity of 1500 kg (3307 lb.).

Hassle-free equipment installation

This rack offers a variety of features that make it easy to install your equipment. With adjustable mounting rails, you can easily change the rail depth from 3 to 37 in. (76.2 mm - 939.8 mm) to support full-depth equipment. The added depth also provides support for additional cable and power management behind your equipment.

The rack features grommet holes on the ceiling and floor panels, which make it easy to run cabling in and out of the cabinet for discreet cable management. The rack also features grounding lugs that enable you to ground your equipment for added protection, and tool-less accessory mounting rails so you can mount 0U vertical cable managers and PDUs.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables tidy. You can cut the self-gripping fabric to any size, and bind your equipment cables together or to the rack.

To provide hassle-free deployment the rack ships fully assembled.

Keep your equipment secure, cool, and accessible

To keep your rack-mounted equipment secure, this rack features front and rear locking mesh doors that also increase airflow to provide passive cooling.

The rack also has a removable side panel with an independent quick-release lock that enables you to access your equipment easily, while still keeping it secure. Plus, a quick-release ceiling panel you can remove without interfering with cable runs that are running through your rack.

Maximum Maneuverability, with casters included

The cabinet features casters, providing ease of mobility around your office, studio or server room. Plus, the width and height of the rack fit through standard doorways, giving you the freedom to wheel your server rack into different rooms as needed.

The RK2537BKM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Deploy in technology shops and repair centers that have limited space but tend to have mountable equipment that requires security
- Install rack-mount servers, KVM switches, networking equipment and cabinet consoles
- House rack-mount audio/video equipment for broadcasting in your editing room or television studio

Features

- Easily install your equipment, with two 0U tool-less mounting panels included
- Keep your rack-mount equipment secure with lockable doors
- Front and side mounting holes to accommodate different types of equipment
- Hassle-free cable management with hook-and-loop cable tie included
- Keep your equipment at an optimal temperature with passive cooling
- Adjustable mounting rails
- 100 x M6 screws and cage nuts included

Hardware	Warranty	5 Years
	Additional Required Tools	Phillips Screwdriver
	Adjustable Mounting Rails	Yes
	Adjustable Size of Built-in Leveling Feet	100 mm [3.94 in]
	Back Door Construction	Steel Mesh
	Back Door Key Lock	Yes
	Back Door Reversible and/or Removable	Removable
	Cable Management	Yes
	Casters	Included
	Fan(s)	No
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel Mesh
	Front Door Key Lock	Yes
	Front Door Reversible and/or Removable	Reversible
		Removable
	Industry Standards	EIA-310-D
	Ladder Offset	0 in [0 mm]
	Ladder Type	G-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	104 - M6
	Rack Type	4-Post
	Side Panel Construction	Solid Steel
	Side Panel(s) Key Lock	Yes
Side Panels Reversible and/or Removable	Removable	
	Removable	
Tools Included	Yes	
U Markings	Yes	
Wallmountable	No	
Performance	Weight Capacity (Rolling)	2320.5 lb [1050 kg]

	Weight Capacity (Stationary)	3315 lb [1500 kg]
Special Notes / Requirements	Note	Includes 1 pairs of keys
Physical Characteristics	Color	Black
	Height with Casters	48.8 in [123.9 cm]
	Internal Depth	42.3 in [107.4 cm]
	Internal Height	43.7 in [1110 mm]
	Internal Width	23.7 in [601 mm]
	Maximum Mounting Depth	35.2 in [893 mm]
	Minimum Mounting Depth	7.1 in [180 mm]
	Product Height	47.2 in [1200 mm]
	Product Length	42.1 in [1070 mm]
	Product Width	23.6 in [600 mm]
	Rail Thickness	0.1 in [2.1 mm]
Packaging Information	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	252.6 lb [114.3 kg]

Product appearance and specifications are subject to change without notice.