

## Wall-Mount Server Rack - 4U

Product ID: RK419WALVO



The RK419WALVO 4U 19-inch Steel Side Mount Rack is a Wall Mountable 4U solid steel rack, providing a robust solution for mounting your telecom, network or server equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This server rack can be mounted in a server room, office, or above a doorway in rooms lacking the floor space for a full-size rack, expanding your workspace and keeping your equipment easily accessible.

The rack is constructed to EIA-RS310 standards and allows equipment to be mounted vertically - non-rackmount equipment can be installed using the rack as a wall case.

The bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16-inches apart, matching standard construction stud measurements for easy installation.

Backed by a StarTech.com Lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a blade server anywhere in an office without a full server room
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

### Features

- Includes optional 4U steel plate that allows rack to be used as a wall case/shelf for any non-rackmount equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- TAA compliant for GSA Schedule purchases
- Compatible with most 19" wide rack mountable equipment
- Made from solid steel for durability
- Constructed to meet the EIA-RS310 19" rack standards

<b>Hardware</b>	Warranty	Lifetime
	Frame Type	Enclosed Cabinet
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	Special Features	Ships Fully Assembled
		Wall-Mountable
	U Height	4U
Wallmountable	Yes	
<b>Performance</b>	Weight Capacity	61.2 lb [27.7 kg]
<b>Physical Characteristics</b>	Color	Black
<b>Product Measurements</b>	Internal Depth	19.5 in [49.6 cm]
	Internal Width	19.5 in [49.6 cm]
	Maximum Mounting Depth	18.9 in [48 cm]
	Product Height	8.2 in [20.9 cm]
	Product Length	22 in [55.8 cm]
	Product Width	19.8 in [50.4 cm]
	Weight of Product	22.1 lb [10 kg]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Package Height	9.2 in [23.3 cm]
	Package Length	22.7 in [57.6 cm]
	Package Width	21.3 in [54 cm]
	Shipping (Package) Weight	26.3 lb [11.9 kg]
<b>What's in the Box</b>	Included in Package	1 - RK419WALVO 4U Wallmount Rack
		16 - #10-32 Screws
		16 - #10-32 Cage Nuts

Product appearance and specifications are subject to change without notice.