

4U 19in Secure Horizontal Wall Mountable Server Rack - 2 Fans Included

Product ID: RK419WALVSGB



The RK419WALVSGB 4U 19-inch Secure Horizontal Wall-Mountable Server Rack is a lockable, solid steel storage rack that provides a robust solution for wall mounting telecom, network or server equipment, and includes two 120mm fans, for improved airflow. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 4U rack can be mounted to a wall in a server room, office, or above a doorway in rooms lacking the space for a full-size rack, to expand your workspace and keep your equipment protected from unauthorized access. The bracket mounting holes (used to mount to a wall or desk) are positioned at 16-inches apart, matching standard stud measurements for easy installation.

Constructed to EIA-RS310 standards, the wallmount server rack allows equipment to be mounted horizontally, and offers a hinged lockable front cover as well as a lockable body. Alternatively, non-rackmount equipment can be mounted vertically with the included bottom cover, using the rack as a wall case.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Includes optional 4U steel plate which acts as a shelf, allowing the rack to be used as a wall case for any non-rackmount equipment
- Hinged, lockable front cover
- TAA compliant for GSA Schedule purchases
- Both the top cover and the rack body are lockable separately for varying security levels
- 2 x 120mm fans included
- Wall mounting holes are 16in center to center, for greater stability and mounting to standard wall studs
- Compatible with most 19in wide rack-mountable equipment
- Solid steel construction
- Constructed to meet the EIA-RS310 19in rack standards

Hardware	Warranty	Lifetime
	Fan Options	Two Fans Included: 120 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel
	Front Door Features	Secure Key Lock with Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	Side Panel Construction	Steel
	Special Features	Grounding Lug(s) Lockable Top Hatch Ships Fully Assembled Wall-Mountable
	U Height	4U
	Wallmountable	Yes
Performance	Airflow Rate	106 CFM
	Audible Noise	46 dBA @ 1 Meter
	Weight Capacity	68 kg [150.3 lb]
Physical Characteristics	Color	Black
Product Measurements	Internal Depth	58.5 cm [23 in]
	Internal Width	48.5 cm [19.1 in]
	Maximum Mounting Depth	52.1 cm [20.5 in]
	Product Height	21.9 cm [8.6 in]
	Product Length	644 mm [25.4 in]
	Product Width	721 mm [28.4 in]
	Weight of Product	19.9 kg [44 lb]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	28.8 cm [11.3 in]
	Package Length	77.4 cm [30.5 in]

	Package Width	71 cm [28 in]
	Shipping (Package) Weight	23.1 kg [51 lb]
What's in the Box	Included in Package	1 - RK419WALVS 4U Wallmount Rack 1 - Set of Keys 1 - UK to EU Plug Converter 24 - #10-32 Screws 24 - #10-32 Cage Nuts

Product appearance and specifications are subject to change without notice.