

## 6U 19in Wallmount Server Rack Cabinet with Acrylic Door

Product ID: RK619WALLGB



The RK619WALLGB Wall-Mounted 6U Server Rack/Cabinet can be fastened to most types of walls and features a sturdy, compact design that can be positioned almost anywhere, without wasting valuable floor space. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This equipment rack offers 6U of storage space and is designed to accommodate 19-inch (wide) servers, networking and telecom equipment. The rack features a 12cm fan, with ventilation positioned above and below the front panel glass door, helping to keep dust out of the rack while ensuring a cool operating environment for your valuable equipment.

To ensure optimum security and prevent tampering with the enclosed equipment, the cabinet/rack features a lockable, smoked acrylic front door that can be removed entirely or installed to open to the left or right as needed.

Backed by a StarTech.com Lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Install rack equipment over doorways, or in tight spaces (e.g. server closets)
- Mount networking and telecommunication equipment to the wall
- Securely protect and wall mount sensitive rackmountable equipment

### Features

- Lockable acrylic door with a large viewing area
- Compact wallmount design and rugged steel construction
- TAA compliant for GSA Schedule purchases
- Vented panels with a 120mm cooling fan
- Large side and bottom cable routing holes with grommets

<b>Hardware</b>	Warranty	Lifetime
	Fan Options	One Fan Included: 120 mm + One Optional Fan: 120 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel with Acrylic Window
	Front Door Features	Secure Key Lock
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	Side Panel Construction	Steel
	Special Features	Ships Fully Assembled Wall-Mountable
	U Height	6U
	Wallmountable	Yes
<b>Performance</b>	Weight Capacity	50 kg [110.5 lb]
<b>Physical Characteristics</b>	Color	Black
<b>Product Measurements</b>	Internal Depth	37.5 cm [14.7 in]
	Internal Width	45.1 cm [17.8 in]
	Maximum Mounting Depth	28.6 cm [11.2 in]
	Product Height	0 cm [0 in]
	Product Length	0 mm [0 in]
	Product Width	0 mm [0 in]
	Weight of Product	10.4 kg [22.9 lb]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Package Height	46.8 cm [18.4 in]
	Package Length	68.5 cm [27 in]
	Package Width	46.5 cm [18.3 in]
	Shipping (Package) Weight	13.3 kg [29.3 lb]
<b>What's in the Box</b>	Included in Package	1 - 6U Wallmount Cabinet 1 - Set of keys

1 - Pack of CAB screws and Cage nuts(20 each)

1 - UK to EU plug converter

20 - M5 Screws

20 - M5 Cage Nuts

---

Product appearance and specifications are subject to change without notice.