

Vertical Wall-Mount Server Rack - Solid Steel - 6U

Product ID: RK619WALLV



This wall-mount bracket provides 6U of storage space to vertically mount your equipment on the wall. The 6U wall-mount rack is EIA-310-D compliant to ensure compatibility with any 19" rack-mount equipment, such as your power strips, telecommunication, network and A/V devices.

Save space by mounting your equipment to the wall or other surface

The 6U rack optimizes your working space by mounting equipment to your wall instead of taking up desk space or other surface area. It's perfect for your SoHo (small office, home office) environment, server room or any other location where available space is limited.

Ensure a secure and hassle-free installation

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your expensive, mission-critical equipment. Also, because the wall mounting holes are positioned 16" apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring. Cage nuts and screws are also included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

Customize your workspace with versatile installation options

To provide a suitable mounting solution for virtually any surface such as your wall, ceiling or desk, the 6U bracket features separate mounting patterns for both ceilings and walls. This means that you can mount the bracket vertically to your wall or horizontally to your ceiling or under your desk.

If you're looking for a mountable storage solution with fewer rack units, StarTech.com also offers a [1U wall-mount bracket](#), a [2U wall-mount bracket](#), a [3U wall-mount bracket](#) and a [4U wall-mount bracket](#).

The RK619WALLV is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Install networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Use in your small office environment where you can't comfortably fit a full-sized rack

Features

- Save space in your office or server room by mounting IT or AV equipment vertically to a wall or horizontally under a desk or work bench
- Hassle-free setup with wall-mount installation holes spaced 16 in. apart, matching standard construction framework
- Easy equipment installation, with cage nuts and screws included
- 6U wall-mount design
- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability

Hardware	Warranty	Lifetime
	Cable Management	No
	Casters	No
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Industry Standards	EIA-310-D EIA RS310-C
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	16 - M5
	Rack Type	2-Post
	Tools Included	No
	U Height	6U
	U Markings	No
	Wallmountable	Yes
Performance	Weight Capacity (Stationary)	200.5 lb [90.7 kg]
Special Notes / Requirements	Note	Package includes 1½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Internal Width	17.7 in [450 mm]
	Product Height	11.1 in [282 mm]
	Product Length	6 in [152 mm]
	Product Weight	2.9 lb [1.3 kg]
	Product Width	19.9 in [505 mm]
	Rail Thickness	0.1 in [2 mm]
Packaging Information	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	4.8 lb [2.2 kg]
What's in the Box	Included in Package	1 - vertical wallmount bracket

16 - M5 cage nuts

16 - M5 screws with washers

6 - wood screws

1 - instruction manual

Product appearance and specifications are subject to change without notice.