

## 6U Vertical Server Cabinet - 30 in. depth

Product ID: RK630WALVS



This 6U vertical server cabinet offers a space-saving way to keep your network and server equipment secure. With its 30 in. depth and a weight capacity of up to 200 lb. (90.7 kg), the server rack/cabinet is designed to fit your needs. It also features an additional 2U mounting bracket positioned toward the top of the enclosure, that you can use to mount patch cables or other shallow rack-mount equipment.

### Free up space

Wall-mount your equipment, even if you don't have enough space for a full-sized rack or cabinet. This low-profile server cabinet is perfect for areas where space is at a premium, such as an office. The cabinet saves space by extending only minimally from the wall and housing the length of your equipment vertically. This reduces the horizontal footprint of your equipment while still providing plenty of room for your servers, patch panels, and switches.

### Keep your equipment cool and secure

To help keep your equipment secure, the vertical server cabinet/network rack features a sturdy metal design and a lock on both the door and access panel. It is also vented, providing passive cooling to help keep your equipment running at suitable temperatures.

**Easy, hassle-free installation**

The server rack comes fully assembled and includes all of the necessary hardware to install equipment, making installation fast and easy. The mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common North American wall-frame stud spacing.

The RK630WALVS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

### Features

- Total load capacity of 200 lb. (90.7 kg)
- Save space by mounting your server vertically to the wall
- Extra 2U of space for switches and patch cables
- Keep equipment secure with lockable door and access panel
- Comes fully assembled with all necessary hardware to install equipment for easy installation
- Provides 6U of storage space

<b>Hardware</b>	Warranty	5 Years
	Additional Required Tools	Phillips Screwdriver
	Adjustable Mounting Rails	Yes
	Back Door Key Lock	No
	Back Door Reversible and/or Removable	No
	Cable Management	Yes
	Casters	No
	Fan(s)	No
	Fans	2 - 120 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Solid Steel
	Front Door Key Lock	Yes
	Front Door Reversible and/or Removable	Reversible
		Removable
	Industry Standards	EIA-310-D
	Ladder Type	C-Shape
	Mounting Holes	Circle, Threaded
	Number and Type of Included Cage Nuts	24 - 12-24
	Rack Type	2-Post
	Side Panel Construction	Solid Steel
	Side Panel(s) Key Lock	No
	Side Panels Reversible and/or Removable	No
	Style	Wall-Mount
Tools Included	No	
U Height	6U	
U Markings	No	
Wallmountable	Yes	
<b>Performance</b>	Weight Capacity (Stationary)	198.9 lb [90 kg]
<b>Special Notes / Requirements</b>	<b>Note</b>	Includes 2 pairs of keys

<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Internal Depth	11.3 in [28.8 cm]
	Internal Height	36.9 in [937 mm]
	Internal Width	25.2 in [641 mm]
	Maximum Mounting Depth	29.9 in [760 mm]
	Product Height	37 in [941 mm]
	Product Length	11.6 in [294 mm]
	Product Weight	72.9 lb [33 kg]
	Product Width	25.4 in [645 mm]
	Rail Thickness	0.1 in [3.1 mm]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	77.4 lb [35 kg]
<b>What's in the Box</b>	Included in Package	1 - wall-mount rack
		2 - door keys
		2 - front-panel keys
		24 - 12-24 screws
		24 - plastic washers
		1 - instruction manual

Product appearance and specifications are subject to change without notice.