

8U Open Frame Wall Mount Equipment Rack - Adjustable Depth

Product ID: RK812WALLOA



The RK812WALLOA 8U Open Frame Wall Mount Equipment Rack with Adjustable Depth is a high-quality, sturdy relay rack solution that is easy to assemble and install into any environment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The open rack features an adjustable depth ranging from 12-20 inches, in order to accommodate larger data, network and telecommunications devices. The greater than average depth of the rack also allows for mounting of shelves and other accessories. The wall mounts are positioned 16in apart (center to center), making it suitable for mounting on virtually any wall surface, based on North American wall frame stud spacing standards.

This 8U rack can be mounted to the wall in a server room, office, or above a doorway, expanding your workspace and keeping your equipment easily accessible.

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Mount Audio/Video broadcast or distribution components
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

Features

- Adjustable rails 12-20" depth options
- Wall mount holes are 16" from center to center for mounting to any standard wooden studs (easily mounts to concrete or steel as well)
- TAA compliant for GSA Schedule purchases
- Package includes necessary hardware for mounting the components
- Low cost rugged design for simple implementation

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	G-Shape
	Rack Type	2-Post
	Special Features	Ships Fully Assembled
		Wall-Mountable
	U Height	8U
Wallmountable	Yes	
Performance	Weight Capacity	135.3 lb [61.2 kg]
Special Notes / Requirements	Note	Hardware to mount the rack to the wall is not provided
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Maximum Mounting Depth	19.7 in [50 cm]
	Product Height	17.9 in [45.5 cm]
	Product Length	12 in [30.5 cm]
	Product Width	19.8 in [50.4 cm]
	Weight of Product	24.4 lb [11.1 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	19.3 in [49 cm]
	Package Length	21.9 in [55.7 cm]
	Package Width	13.8 in [35 cm]
	Shipping (Package) Weight	28.8 lb [13 kg]
What's in the Box	Included in Package	1 - Wall Mount Rack
		16 - Assembly Screws
		16 - M5 Screws
		16 - M5 Cage Nuts
		8 - Truss Head Screws

1 - Installation Guide

Product appearance and specifications are subject to change without notice.