

8U 22in Depth Hinged Open Frame Wall Mount Server Rack

Product ID: RK819WALLOH



The RK819WALLOH 8U 22in Depth Hinged Open Frame Wall Mount Server Rack lets you wall mount your (19-inch wide) servers, A/V or network equipment and features a hinged rack design that allows the entire frame to swing open for easy installation and maintenance of your equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The 8U wallmount rack offers a 4 post design for additional support of your equipment, storing a maximum weight capacity of 63 kg (140 lbs). Constructed of high-quality SPCC cold-rolled steel for strength and durability, the open frame wallmount server rack allows for maximum airflow, and ships complete with all of the rack screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

Features

- 8U Hinged Wall Mount Rack
- Hinged design for easy access to rear panels
- TAA compliant for GSA Schedule purchases
- 4 Post design for added stability
- Open frame design provides additional airflow
- Package includes all necessary screws/nuts for mounting rack equipment
- Sturdy SPCC cold-rolled steel construction

Hardware	Warranty	Lifetime
	Adjustable Mounting Rails	No
	Cable Management	No
	Casters	No
	Fan(s)	No
	Frame Type	Open Frame
	Front Door Construction	Open
	Front Door Key Lock	No
	Industry Standards	EIA-310-D EIA RS310-D
	Ladder Offset	0.7 in [19 mm]
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	24 - 10-32
	Rack Type	4-Post
	Tools Included	No
	U Height	8U
	U Markings	No
	Wallmountable	Yes
	Performance	Weight Capacity (Stationary)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Minimum Mounting Depth	19.8 in [502 mm]
	Product Height	19.2 in [488 mm]
	Product Length	23.7 in [603 mm]
	Product Weight	33.3 lb [15.1 kg]
	Product Width	21.9 in [555 mm]
	Rail Thickness	0.1 in [2 mm]
Packaging Information	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	39.1 lb [17.7 kg]

What's in the Box	Included in Package
	1 - Hinged Wall Mount Rack
	32 - #10-32 UNF Panel Screws
	32 - #10-32 UNF Cage Nuts
	1 - Instruction Manual

Product appearance and specifications are subject to change without notice.