

8U Vertical Server Cabinet - 30 in. depth

Product ID: RK830WALVS



This 8U vertical server cabinet offers a space-saving way to keep your network and server equipment secure. With its 30 in. depth, and a weight capacity of up to 200 lb. (90.7 kg), the server rack/cabinet is designed to fit your needs. It also features an additional 2U mounting bracket positioned toward the top of the enclosure, that you can use to mount patch cables or other shallow rack-mount equipment.

Free up space

Wall-mount your equipment, even if you don't have enough space for a full-sized rack or cabinet. This low-profile server cabinet is perfect for areas where space is at a premium, such as an office. The cabinet saves space by extending only minimally from the wall and housing the length of your equipment vertically. This reduces the horizontal footprint of your equipment while still providing plenty of room for your servers, patch panels, and switches.

Keep your equipment cool and secure

To help keep your equipment secure, the vertical server cabinet/network rack features a sturdy metal design and a lock on both the door and access panel. It is also vented, providing passive cooling to help keep your equipment running at suitable temperatures.

Easy, hassle-free installation

The server rack comes fully assembled and includes all of the necessary hardware to install equipment, making installation fast and easy. The mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common North American wall-frame stud spacing.

The RK830WALVS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office, without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Total load capacity of 200 lb. (90.7 kg)
- Save space by vertically mounting your server to the wall
- Extra 2U of space for switches and patch cables
- Keep equipment secure with lockable door and access panel
- Comes fully assembled with all necessary hardware to install equipment for easy installation
- Provides 8U of storage space

Hardware	Warranty	5 Years
	Fan Options	Two Optional Fans: 120 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel
	Front Door Features	Secure Key Lock with Reversible and Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Threaded Hole
	Mounting Rail Profile	C-Shape
	Rack Type	2-Post
	Side Panel Construction	Steel
	Special Features	Adjustable Mounting Rails
		Lockable Top Hatch
		Ships Fully Assembled
	Wall-Mountable	
	U Height	8U
	Wallmountable	Yes
Performance	Weight Capacity	198.9 lb [90 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
Product Measurements	Internal Depth	14.8 in [37.6 cm]
	Internal Width	25.3 in [64.2 cm]
	Maximum Mounting Depth	29.9 in [76 cm]
	Product Height	37 in [94.1 cm]
	Product Length	15.1 in [38.3 cm]
	Product Width	25.4 in [64.4 cm]
	Weight of Product	80.7 lb [36.5 kg]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	3.3 ft [1 m]
	Package Length	18.1 in [46 cm]
	Package Width	28.3 in [72 cm]

	Shipping (Package) Weight	86.2 lb [39 kg]
What's in the Box	Included in Package	1 - wall-mount rack 2 - door keys 2 - front-panel keys 32 - 12-24 screws 32 - plastic washers 1 - instruction manual

Product appearance and specifications are subject to change without notice.