

Portable Server Rack with Handles - 9U

Product ID: RK960CP



This 9U portable server rack lets you store your server, network and telecommunications equipment in a sturdy mobile rack that has a fixed depth of 23 inches. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Portable design

With built-in handles and four swiveling casters, this mobile rack is easy to transport around your server room, office or studio. Its increased mobility makes this cabinet the ideal solution for telecommunication racks that need to interface with different equipment around your workspace.

Durable construction

The server rack features heavy-gauge mounting rails to ensure a stable installation platform. This durable 4-post rack supports a static loading capacity of up to 220 lb (99.8 kg), and is compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), providing a universal design that's compatible with most rack equipment.

Fast assembly

Save time and hassle with a rack that's easy to put together. With its easy four-step assembly process, you can set this portable rack up in minutes.

The RK960CP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a portable video editing and production rack that you can move around your studio to interface with different equipment
- Store this mobile rack beneath a table or bench in small offices or workspaces
- Mount equipment in technology shops and repair centers where security is required

Features

- Maximum portability with built-in handles and four swiveling casters included
- 9U closed-frame design
- TAA compliant for GSA Schedule purchases
- 23 in. mounting depth
- Supports a static loading capacity of 220 lb (99.8 kg)
- Easy-to-assemble with simple four-step installation

Hardware	Warranty	2 Years
	Cable Management	No
	Casters	Included
	Fan(s)	No
	Frame Type	Enclosed Cabinet
	Industry Standards	EIA/ECA-310-E
	Ladder Type	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Rack Type	4-Post
	Side Panel Construction	Steel
	Special Features	Assembly Required (Flat-Packed) U-Markings
	Tools Included	Yes
	U Height	9U
	Wallmountable	No
	Performance	Weight Capacity (Stationary)
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Height with Casters	22.1 in [562 mm]
	Internal Depth	23.5 in [598 mm]
	Internal Width	19 in [482 mm]
	Maximum Mounting Depth	23.4 in [595 mm]
	Product Height	18.8 in [477 mm]
	Product Length	23.6 in [600 mm]
	Product Weight	53.2 lb [24.1 kg]
Product Width	20.3 in [515 mm]	
Packaging Information	Shipping (Package) Weight	61.5 lb [27.9 kg]
What's in the Box	Included in Package	2 - Side panel with handles
		1 - Top panel
		1 - Bottom panel with grommet

- 8 - Plastic corner caps
- 32 - M5 (10 mm) Phillips flat-head screw
- 24 - M3 (8 mm) Phillips flat-head screw
- 2 - 2.5 in. caster
- 2 - 2.5 in. brake caster
- 16 - M5 (15 mm) bracket screws
- 50 - M5 (12 mm) panel screws
- 50 - M5 cage nut
- 1 - Cage nut tool
- 1 - Phillips screwdriver
- 1 - Phillips bit
- 1 - Instruction manual

Product appearance and specifications are subject to change without notice.