

# Single-Port Rackmount KVM Console with 17" Display

Product ID: RKCONS1701



Providing centralized control of your PC, server, or KVM switch, this single-port rackmount KVM console gives you easy access to your connected system. With a minimal footprint, it mounts in a server rack or cabinet using only 1U of rack space.

## An All-Inclusive Solution

The 1U rackmount console features a built-in keyboard, a touchpad for intuitive control, and a 17-inch LCD display that supports resolutions up to 1280x1024.

This single-port KVM console includes everything you need to set up right out of the box:

- 1 VGA KVM Cable
- Mounting Rails
- M5 Cage Nuts and Screws

## **Simple System Integration**

The rack console features a single-port KVM module, which can be connected directly to a server or PC, or to a KVM switch for access to multiple systems. The KVM module offers the flexibility you need for easily integrating the console into your existing server infrastructure.

## **StarTech.com Rack Consoles**

Rack consoles provide convenient, rack-mounted control options for single servers or entire server rooms. KVM consoles include LCD display, keyboard, and trackpad, all sliding into 1U of rack space. RKCONS1701 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

### Features

- Reduce your server room clutter with a 1U rackmount design
- Intuitive system integration with direct support for your PC or server
- Ready to use with built-in touchpad and keyboard
- Save money and reduce hassle with a cost-effective rackmount LCD console
- Set up easily with all necessary mounting brackets, cables and screws included

<b>Hardware</b>	Warranty	2 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	No
	Display Size	17in
	Front Door Key Lock	No
	KVM Ports	1
	Number of Monitors Supported	1
	Panel Type	Active Matrix TFT LCD
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	Yes
	U Height	1U
	<b>Performance</b>	Aspect Ratio
Brightness		250 cd/m <sup>2</sup>
Color Depth		8-bit, 16.7M colors
Contrast Ratio		1000:1
IP Control		No
Maximum Analog Resolutions		1280 x 1024
Maximum Number of Users		1
MTBF		50, 000 Hrs
Pixel Pitch Support		0.264 x 0.264 mm
Response Time		5ms
Supported Resolutions		Resolutions up to 1280 x 1024 @ 60Hz
Viewing Angle		170° (H), 160° (V)
<b>Connector(s)</b>	Host Connectors	1 - VGA (15 pin, High Density D-Sub) Female Input
<b>Indicators</b>	LED Indicators	1 - Power / Status LED
<b>Power</b>	Input Current	1.5A
	Input Voltage	100 - 240 AC
	Power Consumption (In Watts)	13W
	Power Source	International Power Cords
<b>Environmental</b>	Humidity	10 ~ 80% RH (non-condensing)

	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Cable Length	6ft
	Color	Black
	Enclosure Type	Steel
	Maximum Mounting Depth	31.1 in [79 cm]
	Minimum Mounting Depth	17.7 in [45 cm]
	Product Height	1.7 in [4.3 cm]
	Product Length	18.5 in [47.1 cm]
	Product Width	17.6 in [44.8 cm]
	Weight of Product	25.9 lb [11.7 kg]
<b>Packaging Information</b>	Package Height	7.5 in [19 cm]
	Package Length	30.1 in [76.5 cm]
	Package Width	24.2 in [61.5 cm]
	Shipping (Package) Weight	37.8 lb [17.1 kg]
<b>What's in the Box</b>	Included in Package	1 - KVM console
		1 - KVM cable
		8 - M5 cage nuts
		8 - M5 screws
		5 - regional power cords (NA, JP, UK, EU, ANZ)
		2 - mounting rails
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.