

## 17" HD Rackmount KVM Console - 1 Port

Product ID: RKCONS17HD



Providing centralized control of your single PC or dozens of servers, this HD rackmount KVM console also gives you easy access to and visibility of your system while it's mounted in a server rack or cabinet. Connected to your servers through a separate KVM switch (sold separately), the LCD console installs into 1U of rack-space, offering a space-efficient solution for complete console control.

### High-Definition LCD Monitor

The 1080p KVM console's monitor is 17.3" and LED back-lit, for low power consumption. It supports high-definition resolutions up to 1920x1080 providing sharper video performance. This HD console also provides more screen space, helping you to run multiple applications on the same screen, increasing your productivity.

## **Clutter-Free Monitoring**

The rack-mount LCD console slides out from 1U of rack space, enabling you to easily monitor and control a single server or multiple servers when connected through a KVM switch. The rackmount VGA KVM features a handle that makes it easy to slide the console in and out of the server rack, keeping your area organized and clutter-free.

## **Simple Setup**

This single-port KVM console comes with everything you need to set up:

- 1 Audio Cable
- 1 Set of KVM Cables (VGA)
- 2 Rear Mounting Brackets
- M5 Cage Nuts and Screws

## **Cost Effective Solution**

This KVM console provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in keyboard and a touchpad for intuitive control, as well as a high-definition LCD display.

StarTech.com offers a wide selection of KVM consoles to help you access your systems more efficiently without the expense and clutter of extra peripherals. This rackmount KVM console is backed by a 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Large server farms
- Colocation facilities

### Features

- Save money and reduce hassle with a cost-effective rack-mount LCD console
- Crystal-clear picture quality and maximum screen space with support for resolutions up to 1080p
- Reduce your server room clutter with a 1U rack-mount design
- Intuitive system integration with direct support for a single server or KVM switch
- Built-in touchpad and keyboard

<b>Hardware</b>	Warranty	2 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	No
	Display Size	17.3"
	KVM Ports	1
	Number of Monitors Supported	1
	Panel Type	Active Matrix TFT LCD
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	Yes
	U Height	1U
<b>Performance</b>	Aspect Ratio	16:9
	Brightness	300 cd/m <sup>2</sup>
	Color Depth	6-bit, 262144 colors
	Contrast Ratio	800:1
	IP Control	No
	Maximum Analog Resolutions	1920x1080
	Maximum Number of Users	1
	MTBF	50000 Hours
	Pixel Pitch Support	0.1989 x 0.1989 mm
	Supported Resolutions	Resolutions up to 1920x1080 @ 60Hz
<b>Connector(s)</b>	Host Connectors	1 - HD15 (15 pin, High Density D-Sub) Female Input
	Other Interface(s)	1 - IEC 60320 C14 Power Female Input
<b>Indicators</b>	LED Indicators	1 - Power / Status LED
<b>Power</b>	Input Current	1.5A
	Input Voltage	100 - 240 AC
	Power Consumption (In Watts)	13W
	Power Source	International Power Cords
<b>Environmental</b>	Humidity	10 ~ 80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)

	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Cable Length	1.8 m
	Color	Black
	Enclosure Type	Steel
	Maximum Mounting Depth	33.5 in [85 cm]
	Minimum Mounting Depth	20.1 in [510 mm]
	Product Height	1.7 in [4.3 cm]
	Product Length	22.2 in [56.5 cm]
	Product Width	19 in [48.3 cm]
	Weight of Product	30.3 lb [13.7 kg]
<b>Packaging Information</b>	Package Height	7.3 in [18.5 cm]
	Package Length	30.1 in [76.5 cm]
	Package Width	24.2 in [61.5 cm]
	Shipping (Package) Weight	35.4 lb [16 kg]
<b>What's in the Box</b>	Included in Package	1 - KVM console 1 - KVM cable 8 - M5 cage nuts 8 - M5 screws 5 - regional power cords (NA, JP, UK, EU, ANZ) 1 - quick-start guide 2 - mounting rails

Product appearance and specifications are subject to change without notice.